



+ CONNECTORS

AUTOMOTIVE CONNECTOR CAPS & COVERS



✓ Active

TE CONNECTIVITY (TE)
Straight Wire Dress
MCON Interconnection System

2272976-4
TE Internal Number: 2272976-4

- EU RoHS Compliant
- EU ELV Compliant
- Accessory Type Wire Dress
- Cable Exit Angle 180
- Strain Relief With
- Color Black
- Material PA

↓ **PRODUCT DRAWING**
English

↓ **3D PDF**

DOCUMENTATION

Product Drawings

WIRE DRESS, 6 POSITION, SEALED, MCON 1.2mm FOR STANDARDIZED MOUNTING RAIL
PDF
English

CAD Files

3D PDF
PDF
3D

Customer View Model
2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STP.ZIP

English

Product Environmental Compliance

TE Material Declaration

MD_2272976-4_02202017459_dmtec

PDF

English

Instruction Sheets

Instruction Sheet (U.S.)

1.2-Mm Multiple Contact (MCON) 6-Position Sealed Plug Assemblies 2138387-[]

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Please Note: Use the Product Drawing for all design activity.

Product Type Features

Accessory Type Wire Dress
Strain Relief With
Connector System Wire-to-Wire
Sealable Yes

Configuration Features

Number of Positions 6

Body Features

Cable Exit Angle 180
Color Black
Material PA

Usage Conditions

Operating Temperature Range -40 – 150 °C [-40 – 302 °F]

Industry Standards

UL Flammability Rating None

Packaging Features

Packaging Method Bulk
Packaging Quantity 1

Other

Serviceable Yes

Statement of Compliance

Statement of Compliance
PDF