Part Number : 1300950188
Product Description : Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Long Mesh Length 1.219m (48.00"), Approximate Break Strength 3674.10kg (8100 lbs)
Series Number : 130095
Status : Obsolete
Product Category : Cable Grips
Engineering Part Number : 35960



Documents and Resources

Drawings

1300950188_sd.pdf

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Cable Grips
Series	130095
Description	Medium Duty Wire Mesh Pulling Grip, Single/Double Weave, Bale Eye, Long Mesh Length 1.219m (48.00"), Approximate Break Strength 3674.10kg (8100 lbs)
Product Name	Medium Duty
Type	Pulling Grip
UPC	78678835960

Agency

CSA	LR32159

Physical

Approximate Break Strength	3674.10kg (8100 lbs)
Bale Length	N/A
Body Style	Straight
Cable Diameter	19.05-25.15mm (.750-.990")
Color - Grommet	N/A
Eye Type	Flexible
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	1.219m (48.00")
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

Obsolete

Downloaded from Arrow.com.