

# LQP03TN47NJ04#

Note: If you have not downloaded this document from our official website, please note that the information provided may not be the most current.

Please download the latest datasheet of LQP03TN47NJ04# from the official website of Murata

<http://www.murata.com/en-sg/products/productdetail?partno=LQP03TN47NJ04%23>

"#" at the end indicates the package specification code.

Discontinued



## < List of part numbers with package codes >

LQP03TN47NJ04B

LQP03TN47NJ04D

LQP03TN47NJ04J

## Applications

Unsuitable Applications	Please be sure to read and comply with these "Precautions for use."
Specific Applications	<p>Consumer equipment, Medical equipment [GHTF A/B/C] except for implant &amp; surgery &amp; auto injector, Industrial equipment except for transportation &amp; facility &amp; energy equipment</p> <p>Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, management, and safety required for the above applications, and use Products after confirming the performance and reliability of the actual Product.</p>
Recommended Applications	Consumer equipment



## References

Packaging	Specifications	Standard Packing Quantity
B	Bulk(Bag)	500
D	180mm Paper Tape	10000
J	330mm Paper Tape	50000

### Mass (typ.)

1 piece	0.2mg
---------	-------

## Appearance & Shape



1 of 2

### Attention

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

# LQP03TN47NJ04#

#"at the end indicates the package specification code.

## Specifications

L size	0.6±0.05mm
W size	0.3±0.05mm
T size	0.3±0.05mm
Size code inch (mm)	0201 (0603)
Inductance	47nH±5%
Inductance Test Frequency	300MHz
Rated current (Itemp) (Based on Temperature rise)	50mA
Max. of DC resistance	3.6Ω
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 85°C
Class of magnetic shield	Non-Shielded
Q(min.)	8
Q Test Frequency	300MHz
Self resonance frequency (min.)	1600MHz
Brand	Murata
Series	LQP03TN_04

2 of 2

**Attention**

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, its specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.