Part Number : 885366210
Product Description : MPO QSFP-to-MPO QSFP Fiber Optic Jumper Plenum Cable Assembly, High Bandwidth (OM3), Multimode, 12 Fiber Round Plenum Cable, 10.0m Length
Series Number : 86004
Status : Active
Product Category : Fiber Optic Cable Assemblies



Documents and Resources

Drawings

885366210_sd.pdf

Specifications

885366203-000.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

Downloaded from Arrow.com.

- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Fiber Optic Cable Assemblies
Series	86004
Description	MPO QSFP-to-MPO QSFP Fiber Optic Jumper Plenum Cable Assembly, High Bandwidth (OM3), Multimode, 12 Fiber Round Plenum Cable, 10.0m Length
Connector to Connector	MPO-to-MPO
Mode	Multimode
Product Name	MPO,QSFP
UPC	195842246294

Agency

CSA	LR64395
UL	E72548

Physical

Boot Type	Straight
Cable Length	10.0m
Cable Size	3.00mm
Fiber (Core/Cladding)	50/125µm OM3
Net Weight	98.500/g
Single Ended	No
Wire/Cable Type	12 Fiber Round, Plenum

Downloaded from Arrow.com.