




TIN LEAD PART NUMBER

DD24W7SA00

PART NUMBER

LEAD FREE PART NUMBER

DD24W7SA00LF

PART NUMBER

GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:
SEE DRAWING C01-8639-0003

European Views

rev	ecn no	dr	date
B	-	DEB	2003/10/01
C	LS05-005	MPE	2005/03/16
D	LS06-0095	LGO	2006/06/28
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		mm 	
			TOLERANCES UNLESS OTHERWISE SPECIFIED							
Dr	JARRY	2001/01/26	ANGULAR	LINEAR	0.X	±0.1	size A3	Scale 2		
Eng	PESSON	2001/01/26			0.XX	±0.1				
Chr	LEGARE	2001/01/26			0.XXX	±0.1				
Appr	LEGARE	2001/01/26	0.XX' ±2°		0.XXX ±0.1		ECN		LS06-0095	
			Product family				D-SUB		Spec ref -	
			title SOCKET CONNECTOR 24W7 FOR POWERS CONTACTS			dwg no C01-8639-1855			Rev. D	
catalog no										
			-			CUSTOMER		sheet 1 of 1		