



Part Number : 190670065

Product Description : NylaKrimp Funnel Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 7/16" (M11)

Series Number : 19067

Status : Obsolete


Product Category : Ring and Spade Terminals

Engineering Number : E-958-76

Documents & Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Obsolete
Category	Ring and Spade Terminals

Series	19067
Description	NylaKrimp Funnel Entry Ring Tongue Terminal for 6 AWG Wire, Stud Size 7/16" (M11)
Keyword	Ring Terminal, Ring Terminals
Product Family	Solderless Terminals
Product Name	NylaKrimp
Type	Ring
UPC	800753066199

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	7.472/g
Packaging Type	Bag
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Stud Size	7/16" (M11)
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	10.87mm max.
Wire Size (AWG)	6

Application Tooling

Global

Description	Part Number
Putt Pump Hydraulic Head Crimper, Die Set Required, For Insulated and Non-Insulated Terminals and Splices	<u>192860117</u>
Die Set (Large) for the HHLS Hydraulic Crimper	<u>192890004</u>

PremiumGrade Hand Crimp Tool for 2-8 AWG Terminals	<u>640013900</u>
Crimp Tool Kit for 6 AWG Insulated Ring Terminals	<u>640017770</u>
Putt Pump Dieless Head Crimper, For Insulated and Non-Insulated Terminals and Splices	<u>638162000</u>

This document was generated on Jul 28, 2024