



RP73D2A14K7BTG Product Details

**RP73D2A14K7BTG**

(1-1879277-9)

TE Internal Number: 1-1879277-9



Fixed Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Fixed Resistor
- Resistor Type = Precision Resistor
- Resistance Selection = K Ω
- Resistance = 14.7K Ω
- Power Rating = .125 W

[View all Features](#)

Quick Links

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#)[Request Sample](#)[Find Similar Products](#)[Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Additional Information:

- [Product Line Information](#)

Catalog Pages/Data Sheets:

- [1309350 PASSIVE COMPONENT](#) (PDF, English)
- [SMD Precision Resistors - Type RP73 Series - Tyco El...](#) (PDF, English)
- [8-1773459-4 POWER FILTERING AND RESISTIVE SOLUTIONS ...](#) (PDF, English)

Related Products:

- [Tooling](#)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Fixed Resistor
- Resistor Type = Precision Resistor
- [Element](#) = Thin Film
- [Series](#) = RP73
- Termination Type = Solder

Configuration Features:

- [Number of Terminations](#) = 2
- [Number of Resistors](#) = 1

Electrical Characteristics:

- [Resistance Selection \(\$\Omega\$ \)](#) = K
- [Resistance \(\$\Omega\$ \)](#) = 14.7K
- [Power Rating \(W\)](#) = 0.125
- [Tolerance \(%\)](#) = 0.1
- [Package Type](#) = Cut Tape Length

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Reflow solder capable to 245°C, Reflow solder capable to 260°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Body Features:

- [Mount Style](#) = Surface Mount
- [Packaging Style](#) = 0805
- [Package, Component Size](#) = 2.1 x 1.3

Conditions for Usage:

- [Temperature Coefficient \(ppm/ \$^{\circ}\$ C\)](#) = ± 15

Operation/Application:

- [Application](#) = Precision

Other:

- Brand = Holsworthy

Corporate Information

[Who We Are](#)[Investors](#)[News Room](#)[Supplier Portal](#)[Careers](#)

Quick Links

[Check Distributor Inventory](#)[Cross Reference](#)[Find Documents & Drawings](#)[Product Compliance Support Center](#)[Site Map](#)

Customer Support

[Email or Chat With Us](#)[Find a Phone Number](#)[Search Knowledge Base](#)[Manage your Account](#)

Keep Me Informed

Receive TE News, Events & Technology Updates

Enter your email address 