



+ PASSIVE COMPONENTS

SURFACE MOUNT RESISTORS



✓ Active

TE CONNECTIVITY (TE)

CRGV2010 5% 1M5 3000V

Neohm | CRGV

CRGV2010J1M5

TE Internal Number: 3-1879531-6

[EU RoHS Compliant with Exemptions](#)

[EU ELV Compliant with Exemptions](#)

Resistor Type Power Resistor

Number of Terminations 2

Size Code 2010

Packaging Method Taped & Reeled

Tolerance 5%

[3D PDF](#)

DOCUMENTATION

CAD Files

3D PDF

PDF

3D

Customer View Model

2D_DXF.ZIP

English

Customer View Model

3D_IGS.ZIP

English

Customer View Model

3D_STPZIP

English

Catalog Pages/Data Sheets

1309350_PASSIVE_COMPONENT

PDF

English

FEATURES



Please review product documents or [contact us](#) for the latest agency approval information.

Product Type Features

Resistor Type Power Resistor

Size Code 2010

Element Type Thick Film

Product Type Fixed Resistor

Configuration Features

Number of Resistors 1

Electrical Characteristics

Tolerance 5%

Resistance Range (Ω) 1MΩ – 1GΩ

Resistance (Ω) 1.5M

Power Rating (W) .5

Voltage Rating (V) 200

Termination Features

Number of Terminations 2

Termination Type Solder

Mechanical Attachment

Mount Style Surface Mount

Dimensions

Dimensions (mm) 5 x 2.5 x .55

Usage Conditions

Temperature Coefficient (ppm/°C) ±200

Packaging Features

Packaging Method Taped & Reeled

Other

Comment Max overload voltage 3000V

Statement of Compliance

Statement of Compliance

PDF
