

Downloaded from Arrow.com.


Copyright FCI.


FCIconnect.com

PRODUCT NUMBER	PITCH
EMxx51x000J0G	5.08 mm









Material:

- Item (a) Clamp: Brass(CuZn) Ni plated
- Item (b) Terminal screw: Steel Zinc plating "-" slot type
- Item (c) Female contact: High conductivity copper,Tin plated
- Item (d) Terminal (top body): Thermoplastic (UL94V-0)
- Item (e) Terminal (bottom body): Thermoplastic (UL94V-0)

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 4 Lb-In
- Screw: M3
- Wire strip length: 7-8mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Safety Approval:

Dim A=N×5.08
Dim B=(N-1)×5.08
Dim C=N×5.08+0.2
N=Number of poles

POLES	Tolerance
2p-6p	±0.10
7p-12p	±0.20
13p-18p	±0.30
19p-24p	±0.40

PART NO.: EM xx 51 x 0 00J0 G

Solid block
No. of poles
02 2 poles
03 3 poles
... ...
24 24 poles

Color
0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

RoHS compliant
(lead<4%)
In copper Alloy

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family: TERMINAL BLOCK
ltr	ecn no	dr	date	tolerances unless otherwise specified			title: TERMINAL BLOCK PLUGGABLE PLUG,WITHOUT FLANGE
				angles / linear: X.±0.5		MM	
				X°±1° / X.X±0.3		scale	
				X.XX±0.1			
				dr: EVIN ZHONG 042114			dwg no: EMxx51x000J0G — sheet 1 of 1 — size A4
				engr: EVIN ZHONG 042114			
				chr: HANKE FENG 042114			type: CUSTOMER Drawing
				appd: SHI JUN 042114			
sheet index	revision	A					
	sheet	1					