



 Deutsche Version

[Home](#)

[About Us](#)

Products

Audio

[Video](#)

[Lighting](#)

[Data Connectors](#)

[Industrial](#)

[Support](#)

[News](#)

[Sitemap](#)

Search

☐ PRODUCTS
ONLY

Search

© Neutrik® AG
All rights reserved
[Legal Notices](#)

NEUTRIK



Audio

Phono (RCA)

[back](#)

NYS373-*

Product

Connector Type Jack

Gender female

Electrical

Contact resistance < 10 mΩ

Dielectric strength 0,5 kVdc

Rated current per contact depends on mated connector A

Mechanical

Cable O.D. ≤ 6 mm

Insertion force ≤ 20 N

Withdrawal force > 5 N

Lifetime > 1000 mating cycles

Wire size 24 AWG

Material

Bushing PVC

Contact plating 0.2 μm Au

Contacts Brass (CuZn39Pb3)

Insert Polyamide (PA 6 30 % GR)

Shell Zinc diecast (ZnAl4Cu1) Black

Strain relief Internal plastic chuck

Environmental

Solderability Complies with IEC 68-2-20

Temperature range -20 °C to +70 °C