


RoHS
Compliant

VERSION	DESCRIPTION	DATE
1.0	New Release	2018/4/12



PART NO	DRAWING NO	CABLE LENGTH "L"	COLOR
911M-2-3-00100-G	671-449-A	1000±100	aqua
911M-2-3-00200-G	671-449-B	2000±100	aqua
911M-2-3-00300-G	671-449-C	3000±100	aqua
911M-2-3-00500-G	671-449-D	5000±100	aqua
911M-2-3-00700-G	671-449-E	7000±100	aqua
911M-2-3-01000-G	671-449-F	10000±100	aqua
911M-2-3-01500-G	671-449-G	15000±100	aqua
911M-2-3-02000-G	671-449-H	20000±100	aqua
911M-2-3-02500-G	671-449-I	25000±100	aqua

NOTES:

Insertion loss < 0.3 dB

CnC Tech, LLC
Industrial Cable and Connector Technology

6		Industrial Cable and Connector Technology								
5				TITLE		Patch Cord, LC-LC,MM-50/125 OM3, Duplex, PVC, aqua, 2.0mm, xxm				
4	Dust Cover	UNIT		mm		P/N			DRAWN BY	
3	Shrinkage Tube	unless otherwise stated mm Tolerances XXX.XX ±0.3 ±2° XX.XX ±0.2 X.XX ±0.1		Customer P/N		911M-2-3-0xxxx-G		CHECK BY		
2	LC MM Duplex Connector (Beige housing White boot)									
1	2.0mm,Duplex,MM-50/125 OM3, PVC, Optical Fiber Cable(Aqua)									
No.	Description	SIZE		SCALE		PAGE		1/1		APPROVAL BY
		A4		Free						