

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200710030

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:


Micro-Change (M12) Field Attachable Connector, 8 Poles, Straight, Male, Unshielded, Screw Termination, Cable Diameter 6.00-8.00mm

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120071
Approvals	cRUus - UL Recognized
IP Rating	IP67
Material - Contact	Brass
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Field Attachable Connector
UPC	889056413145
Physical	
Cable Diameter	6.00-8.00mm (.236-.315")
Coupling Type	External Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	Single
Material - Connector Body	PA
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	21.820/g
Orientation	Straight
Poles	8
Temperature Range - Operating	-40°C to +85°C
Wire Size AWG	20
Electrical	
Current - Maximum per Contact	2.0A
Voltage - Maximum	30V
Material Info	
Engineering Number	8A8006-32
Reference - Drawing Numbers	
Sales Drawing	1200710030-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Imidazolidine-2-thione	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

120071 Series

Mates With

1200710031

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION