


Switches

Slide Switches

3.5 (H) mm, 2.0mm-travel

SSSS2 Series

Supports miniaturization and high-density integration for various mobile devices.



- Rating (max.)/(min.) (Resistive load): 0.3A 6V DC/50 μ A 3V DC
 - Contact resistance (Initial performance/After lifetime):
70m Ω max./130m Ω max.
 - Operating life without load: 10,000 cycles 100m Ω max. ※
 - Operating life with load (at max. rated load): 10,000 cycles 130m Ω max. ※
- Note** ※SSSS213202 only 100 cycles

Applications: Healthcare: Healthcare equipment
Home: Major home appliances
Audio_TV: Audio

■ Product List

Products No.	Actuator directions	Travel (mm)	Poles	Positions	Operating force	Changeover timing	Soldering	Dimensions (W×D×H) (mm)	Automotive	Drawing No.
SSSS213000	Vertical	2.0	1	2	Refer to the dimensions.	Non shorting	Manual, Dip	9.0×3.5×3.5	—	1
SSSS211900	Vertical	2.0	1	3	Refer to the dimensions.	Non shorting	Manual, Dip	13.0×3.5×3.5	—	2
SSSS222700	Vertical	2.0	2	2	Refer to the dimensions.	Non shorting	Manual, Dip	9.0×3.5×3.5	—	3
SSSS223600	Vertical	2.0	2	3	Refer to the dimensions.	Non shorting	Manual, Dip	13.0×3.5×3.5	—	4
SSSS213202	Vertical	2.0	1	2	Refer to the dimensions.	Non shorting	Reflow	8.5×3.5×3.5	—	5
SSSS212901	Vertical	2.0	1	3	Refer to the dimensions.	Non shorting	Reflow	13.0×3.5×3.5	—	6
SSSS213100	Horizontal	2.0	1	2	Refer to the dimensions.	Non shorting	Manual, Dip	9.0×3.5×3.5	—	7
SSSS212200	Horizontal	2.0	1	3	Refer to the dimensions.	Non shorting	Manual, Dip	13.0×3.5×3.5	—	8
SSSS212400	Horizontal	2.0	1	4	Refer to the dimensions.	Non shorting	Manual, Dip	15.0×3.5×3.5	—	9
SSSS223200	Horizontal	2.0	2	2	Refer to the dimensions.	Non shorting	Manual, Dip	9.0×3.5×3.5	—	10
SSSS223900	Horizontal	2.0	2	3	Refer to the dimensions.	Non shorting	Manual, Dip	13.0×3.5×3.5	—	11
SSSS224100	Horizontal	2.0	2	4	Refer to the dimensions.	Non shorting	Manual, Dip	15.0×3.5×3.5	—	12
SSSS211603	Horizontal	2.0	1	2	Refer to the dimensions.	Non shorting	Reflow	9.0×3.5×3.5	—	13
SSSS213800	Horizontal	2.0	1	3	Refer to the dimensions.	Non shorting	Reflow	13.0×3.5×3.5	—	14
SSSS224500	Horizontal	2.0	2	3	Refer to the dimensions.	Non shorting	Reflow	13.0×3.5×3.5	—	15

Note

1. This catalog shows only outline specifications. When using the products, please obtain formal specifications for supply.
2. Please place purchase orders per minimum order unit (integer).
3. Please place purchase orders for taping products per minimum order unit (1 reel or a case).

■ Packing Specifications

Bulk

Products No.	Number of packages(pcs.)		Export package measurements (mm)
	1 case / Japan	1 case / export packing	
SSSS213000 SSSS211900 SSSS222700 SSSS223600 SSSS213100 SSSS212200 SSSS212400 SSSS223200 SSSS223900 SSSS224100	2,000	10,000	400 x 270 x 290

Switches


Slide Switches

3.5 (H) mm, 2.0mm-travel

SSSS2 Series


Taping

Products No.	Number of packages(pcs.)			Tape width (mm)	Export package measurements (mm)
	1 reel	1 case / Japan	1 case / export packing		
SSSS213202	1,200	2,400	4,800	24	428 x 413 x 172
SSSS212901	1,000	2,000	4,000	24	406 x 406 x 190
SSSS211603 SSSS213800 SSSS224500	1,400	2,800	5,600	24	406 x 406 x 190




Drawing No.1


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.2


■ Dimensions



■ Mounting Hole Dimensions



■ Circuit Diagram



Viewed from direction A in the dimensions.


Switches

Slide Switches


3.5 (H) mm, 2.0mm-travel
SSSS2 Series

Drawing No.3


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.4


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.5


■ Dimensions



■ Land Dimensions



■ Circuit Diagram



Viewed from direction A in the dimensions.


Switches

Slide Switches


3.5 (H) mm, 2.0mm-travel
SSSS2 Series

Drawing No.6


■ Dimensions



■ Land Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.7


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.8


■ Dimensions



■ Mounting Hole Dimensions



■ Circuit Diagram



Viewed from direction A in the dimensions.


Switches

Slide Switches


3.5 (H) mm, 2.0mm-travel
SSSS2 Series

Drawing No.9


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.10


■ Dimensions



■ Mounting Hole Dimensions




■ Circuit Diagram




Viewed from direction A in the dimensions.

Drawing No.11


■ Dimensions



■ Mounting Hole Dimensions



■ Circuit Diagram




Viewed from direction A in the dimensions.


3.5 (H) mm, 2.0mm-travel
SSSS2 Series

Drawing No.12

■ Dimensions




■ Mounting Hole Dimensions




Viewed from direction A in the dimensions.

- Circuit Diagram




Drawing No.13

- Dimensions




■ Land Dimensions




Viewed from direction A in the dimensions.

- Circuit Diagram




Drawing No.14

■ Dimensions




- Land Dimensions



Viewed from direction A in the dimensions.

- Circuit Diagram




3.5 (H) mm, 2.0mm-travel


SSSS2 Series

Drawing No.15


■ Dimensions



■ Land Dimensions



■ Circuit Diagram



Viewed from direction A in the dimensions.