




DATE	REV	REVISION CHANGES	ECN	APPROV BY
3/11/21	A0	AS DRAWN	-	BTS

- NOTES:
- CONNECTOR MATERIALS:
 - HOUSING: PBT, GREEN
 - CONTACTS: COPPER ALLOY, GOLD PLATED
 - SHELL: COPPER ALLOYS, NICKEL PLATED
 - PIN HOLDER: PBT, BLACK
 - O-RING 1: NBR
 - O-RING 3: EPDM
 - SCREW NUT: COPPER ALLOY, NICKEL PLATED
 - MOUNTING NUT: COPPER ALLOY, NICKEL PLATED
 - FOR PRODUCT SPECIFICATIONS SEE PRO39-01
 - DIMENSIONS AND TOLERANCES COMPLY WITH IEC 61076-2-109 STANDARD
 - CODING TYPE: X
 - CURRENT RATING: 0.5 AMPS MAX PER CONTACT
 - VOLTAGE RATING: 48V PER CONTACT
 - DEGREE OF PROTECTION: IP68

SS-12400-004
PART NUMBER

THIRD ANGLE PROJECTION		11118 Susquehanna Trail South Glen Rock, PA 17327-9199 (717) 235-7512 http://www.stewartconnector.com
DO NOT SCALE DRAWING DRAWING IS SUBJECT TO CHANGE WITHOUT NOTICE	FILE: M12 X-Code, Right Angle, Rear Mount PCB Receptacle	
DIMENSIONS: METRIC	THIS DRAWING AND THE SUBJECT MATTER SHOWN THEREON ARE CONFIDENTIAL AND THE PROPRIETARY PROPERTY OF STEWART CONNECTOR AND SHALL NOT BE REPRODUCED, COPIED, OR USED IN ANY MANNER WITHOUT PRIOR WRITTEN CONSENT OF STEWART CONNECTOR. ONE OR MORE U.S. PATENTS MAY APPLY TO THIS PRODUCT. FOR DETAILS, PLEASE VISIT: HTTP://REFUSE.COM/STEWART/STEWART_PATENTS/	OWN BY: JE DATE: 03/8/21 APPROV BY: BTS DATE: 03/11/21 DWG NO: CT120017 REV: A0
SHEET NO. 1 OF 1		



AutoCAD A1 Metric