



Part Number : [08701040](#)
Product Description : 2.50mm Pitch Mini-SPOX Crimp Terminal, 28-22 AWG, Bag
Series Number : 5263
Status : Active
Product Category : Crimp Terminals
Engineering Number : 5263PBTB
Packaging Alternative : [08701039 \(Reel\)](#)



Documents & Resources

Drawings
[008701040_sd.pdf](#)

3D Models and Design Files
[008701040_stp.zip](#)

Specifications
[52639200-SPK-200.pdf](#)
[52641001-PS-000.pdf](#)
[PS-5264-001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Compliant with Exemption 44; 34
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements
- Eu RoHS
- REACH SVHC

- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	5263
Description	2.50mm Pitch Mini-SPOX Crimp Terminal, 28-22 AWG, Bag
Application	Signal
Product Name	Mini-SPOX
UPC	800753534919

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	43.200/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.90mm max.
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
Mini-SPOX Single Row Receptacle Housings	<u>5264</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for SPOX, MX64, Ditto, MX150CE, Milli-Grid Terminals	<u>638131400</u>
Hand Crimp Tool for 2.50mm Pitch SPOX Crimp Terminal, 28-22 AWG	<u>638281900</u>

Application Tooling

Japan

Description	Part Number
Hand Crimp Tool JHTR5974	<u>11260167</u>

This document was generated on Mar 21, 2025