



Quality Products. Service Excellence.

Equipment Storage Rack Cabinet *C2RR Series*

1,500 lbs|680 kg Weight Capacity



Features

- Constructed in:
 - 14-gauge steel (body)
 - 16-gauge steel (doors and side panels)
 - 10-gauge steel (tapped mounting rails)
 - 12-gauge steel (square hole mounting rails)
- Finished in a rugged, textured powder paint finish.
- Tested to nearly double the suggested load rating of 1,500 lbs (680 kg).
- TAA Compliant.
- RoHS Compliant.
- Manufactured in North America.
- **All configurations include:**
 - One (1) Welded C2 Cabinet Frame
 - Two (2) Removable Side Panels (with 1/4 turn latches)
 - Four (4) Leveling Feet
 - Eight (8) Keys
 - Starter pack of 10-32 Screws (and cage nuts when applicable).
- **C2RR Series Specific Components Include:**
 - Four (4) Infinitely Adjustable - Tapped 10-32 Combination Mounting Rails
 - One (1) Solid Locking Door (Can be used as either front or rear door)
 - One (1) Solid Top Panel
- **C2RR "D" Series Specific Components include:**
 - Four (4) Infinitely Adjustable - Tapped 10-32 Combination Mounting Rails
 - One (1) Window Front Locking Door
 - One (1) Louvered Rear Locking Door
 - One (1) Vented Top Panel with Four (4) 3.5" (89 mm) diameter cable access holes with covers

Gallery



Accessories

- C2 Doors
- Door Adapter Cable Entry Kit
- Side Panel Locking Kit
- Cabinet Baying/Ganging/Joining Kit
- Rack Mount Locking Storage Drawer
- Vertical Cable Tray
- Door Adapter Rack Mount Kit
- Cabinet Fan Tops
- Cabinet Door Replacement Lock
- Shelves
- Vertical Cable Manager with Door
- Cable Lacing Bar

- Horizontal Lacing Strip
- Horizontal Ring Cable Manager
- Outlet Strips
- Grounding
- Cabinet Caster Set
- Horizontal Hinged Cable Manager
- Cable Management Arm
- Mounting Hardware
- Rack Panels
- Medium Caster Set

C2RR Rapid Rack

Part No. Black	Part No. RAL 7035 Light Gray	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
		Height	Width	Depth		Height	Width	Depth
C2RR194223BK1	C2RR194223LG1	50.16	23.00	23.62	24U	42.06	19.00	21.63
C2RR194231BK1	C2RR194231LG1	50.16	23.00	31.50	24U	42.06	19.00	29.50
C2RR196323BK1	C2RR196323LG1	71.16	23.00	23.63	36U	63.06	19.00	21.63
C2RR196331BK1	C2RR196331LG1	71.16	23.00	31.50	36U	63.06	19.00	29.50
C2RR197023BK1	C2RR197023LG1	78.16	23.00	23.62	40U	70.06	19.00	21.63
C2RR197031BK1	C2RR197031LG1	78.16	23.00	31.50	40U	70.06	19.00	29.50
C2RR197823BK1	C2RR197823LG1	86.91	23.00	23.62	45U	78.81	19.00	21.63
C2RR197831BK1	C2RR197831LG1	86.91	23.00	31.50	45U	78.81	19.00	29.50

Overall height includes leveling feet.

C2RR "D" Series LAN/Data Rapid Rack

Part No. Black	Part No. RAL 7035 Light Gray	Overall Dimensions			Rack Units	Usable Mounting Dimensions		
		Height	Width	Depth		Height	Width	Depth
C2RR197023DBK1	C2RR197023DLG1	77.31	23.00	23.63	40U	70.06	19.00	21.63
C2RR197031DBK1	C2RR197031DLG1	77.31	23.00	31.50	40U	70.06	19.00	29.50
C2RR247023DBK1	-	77.31	28.00	23.63	40U	70.06	24.00	21.63
C2RR247031DBK1	-	77.31	28.00	31.50	40U	70.06	24.00	29.50
C2RR197823DBK1	C2RR197823DLG1	86.06	23.00	23.63	45U	78.81	19.00	21.63
C2RR197831DBK1	C2RR197831DLG1	86.06	23.00	31.50	45U	78.81	19.00	29.50
C2RR247823DBK1	-	86.06	28.00	23.63	45U	78.81	24.00	21.63
C2RR247831DBK1	-	86.06	28.00	31.50	45U	78.81	24.00	29.50

Overall height includes leveling feet.

Tags: **Contempra II, Test Rack, Equipment Rack, Automotive Rack, Terminal Rack, Electronics Rack, Instrument Cabinet, System Rack, Audio Rack, Radio Rack**

Data subject to change without notice

© 2019. Hammond Manufacturing Ltd. All rights reserved.