samtec



SBS–120–01–S–DH–WT–ML

(0,80mm) .0315"

SBS-DH SERIES

RIGHT ANGLE BLADE SOCKETS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?SBS-DH

Insulator Material:
Black Liquid Crystal Polymer

FILE NO. E111594

Contact:
BeCu

Plating:
Au over 50µ" (1,27µm)
Ni on contact

Current Rating:
3.1A @ 30°C Temperature Rise

Operating Temp:
-55°C to +125°C

RoHS Compliant:
Yes


Processing:

Lead–Free Solderable:
Yes


SMT Lead Coplanarity:
(0,10mm) .004" max

Mates with:
SiliconSystems SiliconBlade products


EDGE R·A·T·E™ CONTACT



APPLICATION



SBS	–	1	NO. OF PINS PER ROW	–	CARD THICKNESS	–	PLATING OPTION	–	DH	–	WT	–	OTHER OPTION
			20		–01 = (1,60mm) .062" thick card		–S = 30µ" (0,76µm) Gold on contact, Matte Tin on tail		–DH = Double Horizontal		–WT = Weld Tab		–ML = Metal Latch



Note: Some lengths, styles and options are non-standard, non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

Downloaded from Arrow.com.