

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1800812330

Status:

Active

Overview:

Down Light Modules

Description:

Down Light Module 80mm, Flood - 32°, Warm White (3000K), High Flux

Documents:

3D Model

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Product Literature (PDF)

Installation Guide (PDF)

Agency Certification	
UL	E328924
General	
Product Family	Solid State Lighting
Series	180081
Array Type	N/A
Beam Angle	24°, 32°, and 50°
Comments	Commercially Configurable to 700mA, 1050mA, and 1400mA
Installation Guide Order No	987650-4385
Overview	Down Light Modules
Product Literature Order No	987650-4381
Product Name	Down Light Module
Type	LED Puck Module
UPC	884982218956
Physical	
Base Type	Socket
Color Rendering Index (CRI)	82
Correlated Color Temp (CCT)	3000K
Lamp Type	Light Module
Net Weight	64.640/g
Packaging Type	Individual Carton
Electrical	
Lamp Wattage - Maximum	12W, 18.8W, 25.8W
Lumens	1040, 1330, 730
Voltage (Fixture) - Maximum	17.2V, 17.9V, 18.5V
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-180081-000



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

180081 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION