© 2026 TE Connectivity Ltd. family of companies. All Rights Reserved

1757824-6

ACTIVE

104 Position, Receptacle, Cable-to-Cable, Panel Mount, Shell Size 6, 2.29 mm [.09 in] Centerline, Wire & Cable, Signal, -55 – 125 °C [-67 – 257 °F]



AMPLIMITE

TE Internal #: 1757824-6
TE Internal Description: AMPLIMITE,ASY,RCPT,STD,90,ZN,6
Mil-Spec: M24308/2-291Z

Number of Positions : 104
Connector & Housing Type : Receptacle
Connector System : Cable-to-Cable
Connector Mounting Type : Panel Mount
Connector Shell Size : 6

Add to List

Similar Products

Compatible Parts & Tooling

We are here to help!
Get in touch with our product experts.

CHAT WITH US

EMAIL US

CALL US

Feedback

Documents | Features | Product Compliance

Product Drawings

AMPLIMITE RECEPTACLE ASSY,SIZE 1 THRU 6 SERIES 90 WITH ZINC PLATED SHELLS
ENG_CD_1757824_F.Pdf
English

CAD Files

3D PDF
3D_CVM_CVM_1757824-6_J.pdf
3D

Customer View Model
ENG_CVM_CVM_1757824-6_J.2d_dxf.zip
English
ENG_CVM_CVM_1757824-6_J.3d_igs.zip
English
ENG_CVM_CVM_1757824-6_J.3d_stp.zip
English

Datasheets & Catalog Pages

1308940_Sec8_amplimite
ENG_CS_1308940_Sec8_amplimite_0118.pdf
English

Downloaded from Arrow.com.

Product Change Notification

View Product Change Notification

Login required to access product change notifications

REPORT PRODUCT DATA ERROR

Compatible Parts

Filter By Specification



ACCESSORY

204351-1

Gold (Au), Socket Contact, 28 – 22 AWG, .08 – .4 mm²...

From: 1.870

In-Stock

ADD TO CART

Products with Similar Specs

View All Similar Products

THIS PRODUCT

D-SHAPED CONNECTORS

1757824-6

104 Position, Receptacle, Cable-to-Cable, Panel Mount, Shell Size 6,



From $57.560 In-Stock

Number of Positions : **104**
Connector & Housing Type : **Receptacle**
Connector System : **Cable-to-Cable**
Connector Mounting Type : **Panel Mount**
Connector Shell Size : **6**

Top Results

D-SHAPED CONNECTORS

204508-1

78 Position, Receptacle, Cable-to-Cable, Panel Mount, Shell Size 5,



From $25.790 In-Stock

Number of Positions : **78**
Connector & Housing Type : **Receptacle**
Connector System : **Cable-to-Cable**
Connector Mounting Type : **Panel Mount**
Connector Shell Size : **5**

D-SHAPED CONNECTORS

204511-1

104 Position, Plug, Cable-to-Cable, Panel Mount, Shell Size 6, 2.29 mm...



In-Stock

Number of Positions : **104**
Connector & Housing Type : **Plug**
Connector System : **Cable-to-Cable**
Connector Mounting Type : **Panel Mount**
Connector Shell Size : **6**

D-SHAPED CONNECTORS

204506-1

62 Position, Receptacle, Cable-to-Cable, Panel Mount, Shell Size 4,



In-Stock

Number of Positions : **62**
Connector & Housing Type : **Receptacle**
Connector System : **Cable-to-Cable**
Connector Mounting Type : **Panel Mount**
Connector Shell Size : **4**

Customers Also Bought

Downloaded from Arrow.com.



TE Part #: **55A0111-26-2**

600 V, Tin-Coated Copper, 26 AWG, -65 – 150 °C [-85 –...

View Product



TE Part #: **382A023-25/225-0**

Y Shape Cable Transistion, 3 Branches , 25 Material...

$47.490 per unit

Inventory: In-Stock

Add To Cart



TE Part #: **8-35247-2**

Closed Ring Tongue Terminal, 8 AWG, 1/4 / M6 Stud...

$2.972 per unit

Inventory: In-Stock

Add To Cart



TE Part #: **204370-2**

Gold (Au), Pin Contact, 28 – 22 AWG, .08 – .4 mm²...

$0.810 per unit

Inventory: In-Stock

Add To Cart

Downloaded from Arrow.com.