



## 1103427-1 Product Details

[Share](#) | [Print](#) | [Email](#)


1103427-1

TE Internal Number: 1103427-1

Active

View 3D PDF

### HTS Connectors and Accessories

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- HC.26 Series, Power4Net Series
- Insert
- For Use With Motorman, For Use With Power4Net
- Contact Configuration = Crimp Terminal
- Insert Style = Socket

[View all Features](#)

### Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) | [Request Sample](#) | [Find Similar Products](#) | [Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- [FEMALE INSERT ASS'Y SERIES HC26, 4-POS., 22DF POWER ... \(PDF, English\)](#)

#### Catalog Pages/Data Sheets:

- [1773463-1\\_POWER4NET\\_HYBRID\\_CONNECTOR \(PDF, English\)](#)

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files: (CAD Format & Compression Information)

- [2D Drawing \(DXF, Version F\)](#)
- [3D Model \(IGES, Version F\)](#)
- [3D Model \(STEP, Version F\)](#)

[List all Documents](#)

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- Product Type = Insert
- Gender = Female
- Finish = Silver
- Color = Gray

#### Termination Features:

- Termination Method = Standard

#### Body Features:

- Insert Style = Socket
- Wire Range (mm [AWG]) = 0.08-0.40<sup>2</sup> [28-22]
- Material = PBT-GF10

#### Contact Features:

- Contact Configuration = Crimp Terminal
- Number of Poles = 4

#### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- [RoHS/ELV Compliance History](#) = Always was RoHS compliant
- [Approved Standards](#) = DIN EN 60664-1, DIN EN 61984

#### Conditions for Usage:

- For Use With = Motorman, Power4Net

#### Packaging Features:

- Packaging Method = Loose Piece/Bulk

#### Other:

- Series = HC.26, Power4Net
- Brand = TE Connectivity
- Comment = For wire shielding diameter 4.2 (.165).; See drawing for additional product information.; Contacts sold separately.

### Corporate Information

- [About TE](#)
- [Investors](#)
- [News Room](#)
- [Supplier Portal](#)
- [Careers](#)
- [Terms & Conditions](#)
- [Privacy Policy](#)

### Quick Links

- [Distributor Inventory](#)
- [Product Cross Reference](#)
- [Documents & Drawings](#)
- [Product Compliance Support Center](#)
- [Site Map](#)

### Customer Support

- [Email or Chat With Us](#)
- [Find a Phone Number](#)
- [Knowledge Base](#)
- [Manage Your Account](#)

### Keep Me Informed

