

PTC/CAD

REVISIONS

ISSUE
1

CATALOG LISTING


LSQUC5K272

1 OF 1



PAGE

REPLACES


RELEASE NO. PR-22817



CORROSION RESISTANT
STAINLESS STEEL SHAFT
WITH STRAIGHT KNURL



OPERATING DATA - SIDE ROTARY



THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH		THIRD ANGLE PROJECTION	
CHARACTERISTICS		SCALE FULL	
OPERATING TORQUE ----- 4 IN LBS MAX		DO NOT SCALE PRINT	
FULL TRAVEL TORQUE ----- 4 IN LBS MAX		UNLESS OTHERWISE SPECIFIED TOLERANCES ARE	
TOTAL TRAVEL ----- 85° REF		ONE PLACE (.0) ±.030	
PRETRAVEL ----- 5° MAX		TWO PLACE (.00) ±.015	
DIFFERENTIAL TRAVEL ----- 3° MAX		THREE PLACE (.000) ±.005	
OVERTRAVEL ----- 80° MIN		ANGLES ±	
		WEIGHT	

- NOTES
1 - WOODHEAD 5 PIN MINI CONNECTOR
2 - BASIC SWITCH TERMINAL AREA AND CONNECTOR EPOXY SEALED IN HOUSING

ANSI Y14.5M-1982 APPLIES