

LGH Lead Assemblies and Receptacles, 25 KVDC, LGH 1 L (Continued)

Lead Assemblies (Continued)

Description	Assembly Length	Part Numbers			
		Polycarbonate Cap	Glass-Filled Polyester Cap	Glass Epoxy Cap	Metal Cap
Single End Lead Assemblies	6 152.4	2-830637-1	2-863705-1	—	—
	12 304.8	1-830637-2	1-863705-2	—	—
	18 457.2	1-830637-3	1-863705-3	—	—
	24 609.6	2-830637-8	2-863705-8	—	—
	36 914.4	830637-5	863705-5	—	—
	48 1219.2	2-830637-4	2-863705-4	—	—
	6 152.4	—	863706-2	830638-2	—
Double End Lead Assemblies	12 304.8	1-830638-5	1-863706-5	—	—
	18 457.2	2-830638-0	2-863706-0	—	—
	24 609.6	830638-9	863706-9	—	—
	36 914.4	830638-6	863706-6	—	—
	48 1219.2	1-830638-9	1-863706-9	—	—
	6 152.4	862551-1	863707-1	—	—
	12 304.8	862551-4	863707-4	—	—
Single End Lead Assemblies (with Positive Stop Ferrules)	18 457.2	862551-6	863707-6	—	—
	24 609.6	862551-8	863707-8	—	—
	36 914.4	1-862551-5	1-863707-5	—	—
	48 1219.2	1-862551-2	1-863707-2	—	—
	6 152.4	—	—	862552-1	—
	12 304.8	862552-4	—	—	—
	18 457.2	862552-6	—	—	—
Double End Lead Assemblies (with Positive Stop Ferrules)	24 609.6	862552-8	—	—	—
	36 914.4	1-862552-3	—	—	—
	48 1219.2	1-862552-0	—	—	—
	18 457.2	—	—	2-846938-0	—
	24 609.6	—	—	2-846938-1	—
	36 914.4	—	—	1-846938-6††	—
	48 1219.2	—	—	846938-8†	—
Shielded Single End Lead Assemblies	12 304.8	—	—	849616-7	—
	18 457.2	—	—	1-849616-5	—
	36 914.4	—	—	1-849616-0*	—
	60 1524.0	—	—	2-849616-2*	—
Shielded Double End Lead Assemblies	12 304.8	—	—	—	861813-1
	24 609.6	—	—	—	861813-2
	48 1219.2	—	—	—	861813-5
	12 304.8	—	—	—	861814-1
RFI Shielded Single End Lead Assemblies**	18 457.2	—	—	—	1-861814-9
	24 609.6	—	—	—	2-861814-1
	36 914.4	—	—	—	1-861814-5
	48 1219.9	—	—	—	861814-1

*Two equal length ground leads.

**These RFI Shielded Lead Assemblies mate with Receptacle Part Number 861255-1.

†One ground lead, pigtail end only.

††One ground lead, terminated end only. Pigtail End 13 [330.2].