<img height="1" width="1" style="display:none;" alt="" src="https://dc.ads.linkedin.com/collect/?pid=39563&fmt=gif"> <img height="1" width="1" style="display:none" src="https://www.facebook.com/tr?id=890724887782932&ev=PageView&noscript=1">



# UTP28X5BU

Share

## Copper Patch Cord

Category 6A Performance, 28AWG, UTP Patch Cord, CM/LSZH, Blue, 5ft.

Find A Distributor

Qty

Add to Bom

Specifications | Packaging Detail | Resources

Related Products | Top of Page

## Specifications

| | |
|---|---|
| Conductor Gauge (AWG) | 28 |

Downloaded from Arrow.com.

| | |
|---|---|
| Performance Level | Category 6A |
| Conductor Type | Solid |
| Overall Length (In.) | NA |
| Overall Length (ft.) | 5 |
| Overall Length (m) | 1.5 |
| Overall Length (mm) | NA |
| Nominal Diameter (mm) | NA |
| Wiring Scheme | T568B |
| Maximum Operating Temperature (°C) | 75 |
| Maximum Operating Temperature (°F) | 167 |
| Minimum Operating Temperature (°C) | -10 |
| Minimum Operating Temperature (°F) | 14 |
| Maximum Storage Temperature (°C) | 70 |
| Maximum Storage Temperature (°F) | 158 |
| Minimum Storage Temperature (°C) | -40 |
| Minimum Storage Temperature (°F) | -40 |
| Boot Color | Clear |
| Color | Blue |
| Sub Brand | PanNet |
| Flammability Rating | CM, LSZH-1 (60332-1) |
| Standards Met | IEEE 802.3af, 802.3at, 802.3bt type 3 and type 4, UL 1863. |
| Product Type | Copper Patch Cord |
| Cable Color | Blue |
| Length (ft.) | 5.00 |
| Termination End 1 | Modular Plug |
| Termination End 2 | Modular Plug |
| CE Compliant | Yes |
| Nominal Cable Outside Diameter (In.) | 0.19 |
| Nominal Cable Outside | 4.7 |

Downloaded from Arrow.com.

| | |
|---|---|
| Diameter (mm) | |
| Cable Length (ft.) | 5.00 |
| Cable Type | F/UTP |
| Conductor Material | Copper |
| Material | Copper |
| Maximum Installation Temperature (°C) | 70 |
| Maximum Installation Temperature (°F) | 158 |
| Minimum Installation Temperature (°C) | -40 |
| Minimum Installation Temperature (°F) | -40 |
| Part Features | 100% performance tested for wire map, NEXT and return loss, Centered de-embedded plug, Integral pair manager, Patented tangle-free latch |
| RoHS Compliancy Status | Compliant |
| Min. Order Qty. | 1 |
| Measurement System | Feet (USA Only) |

## Packaging Detail

| | |
|---|---|
| UPC | 07498399981 |
| Std. Pkg. Qty. | 1 |
| Std. Pkg. Volume (cf) | 0.0170 |
| Std. Ctn. Qty. | 10 |
| Std. Ctn. Volume (cf) | 0.1703 |


## Resources

| | | | | | |
|---|---|---|---|---|---|
| Specification Sheets | TX6A-28™ Category 6A Performance 28 AWG UTP Patch Cords | US English | View PDF (190.34KB) | Download PDF | Share PDF |
| Technical References | Patch Cord Wiring Guide: TR103 | US English | View PDF (262.81KB) | Download PDF | Share PDF |

Downloaded from Arrow.com.


| | | | | | |
|---|---|---|---|---|---|
| Installation Documents | Panduit 28 AWG Patch Cords Installation Guideline | US English | View PDF (198.34KB) | Download PDF | Share PDF |
| Part Drawings | Category 6A UTP 28 AWG Copper Patch Cords - (CM/LSZH) | US English | View PDF (301.53KB) | Download PDF | Share PDF |
| Selection Guides | 28 AWG Selection Guide - Category 6A, 6, & 5e (NA, LA): COSG10--WW-ENG | US English | View PDF (631.55KB) | Download PDF | Share PDF |
| Selection Guides | Patch Cord Selection Guide (All Regions): COSG11--WW-ENG | US English | View PDF (292.58KB) | Download PDF | Share PDF |
| Application Guides | Panduit Patch Cord Guide: COAG05--SA-ENG | US English | View PDF (335.03KB) | Download PDF | Share PDF |

## Related Products



### UTPSP7BUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 7 ft.



### UTPSP2MBUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 2 meters.

Downloaded from Arrow.com.

## UTPSP5BUY

Category 6, UTP patch cord with TX6™ PLUS Modular Plugs on each end. Blue, 5 ft.

**Email Support**

Email support available 24/7

**800-777-3300**

Monday through Thursday 7:00 am-6:30 pm CST Friday 7:00 am-6:00 pm CST

**Where to Buy**

Find a Panduit Distributor or Partner



Get Our Catalog

Download the PDF or request a copy be mailed to you.

Which catalog would you like'

Download


Copyright 2019 Panduit

Legal Information Privacy Policy Unsubscribe

Downloaded from Arrow.com.