



Products

applications

■ products

Product Type Search
Threat Search
Parameter Search
Check Distributor Inventory
Order Samples
Order Literature
Standards
Environmental Compliance
Obsolete Parts
Quality Assurance
Product News
New Products and Promotions

Reference

Part: 267010**Series:** [267 Series - FM08 Very Fast-Acting Military Fuses \(commercial equivalent - 265 Series\)](#)**Technology:** High Reliability and Military

PARAMETERS

Package Type	Pkg Type	Axial Leaded
Mount Method	Mount	Through Hole
Lead-Free	Pb Free	N
Package Size/Form Factor	Size	PICO
Military/Federal Standards/DSCC Number	Standard #	MIL-PRF-23419/8
Fuse Opening Characteristic	Opening	Very Fast-Acting
Cap Plating	Plating	
Current Rating	Amp Rating (A)	10.0000
Voltage Rating	Voltage Rating (V)	125
Nominal Cold Resistance	Resistance (Ohms)	
Check Distributor Stock		[Check]
Request a Sample		[Add To Cart]

Series Datasheets

**Military Components**

MILFUSES.pdf (162 K)

Last Updated: May 16, 2005

**Protects
Against:
Other
Threats**
Short
Circuit/
Current
Overload

 Click
the
PDF icon
to make a
PDF of
this page