Part Number : 1300980034
Product Description : MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437")
Series Number : 130098
Status : Active
Product Category : Cable Grips
Engineering Part Number : 5508



Documents and Resources

Drawings

1300980034_sd.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Cable Grips
Series	130098
Description	MAX-LOC Strain Relief Cord-Sealing Grip, 3/8" NPT, Straight Male, Cable Diameter 9.53-11.10mm (.375-.437")
NEMA Rating	NEMA 3R
Product Name	MAX-LOC
Type	Strain Relief Grip
UPC	78678872114

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	N/A
Bale Length	N/A
Body Style	Straight
Cable Diameter	9.53-11.10mm (.375-.437")
Color - Grommet	Green
Eye Type	N/A
Gender	Male
Material - Body	Nylon
Material - Grip	N/A
Mesh Length	N/A
Number of Holes	1
O-Ring	No
Thread Size	3/8" NPT

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
MAX-LOC Lock Nut 3/8" NPT	1300990142
MAX-LOC Gasket Sealing Ring, 3/8" NPT, Black	1300990148

Downloaded from Arrow.com.