

5

4

3


2

1


Mating face according to : MIL-C-24308 / DIN 41652 / CECC 75301-802

No1. contact



12,5 max.



screw lock thread



Printed board layout
component side



A

							Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, High temperature, 25 poles, male, straight, with solder pins 2,9 and screw lock.	Maßstab/ Scale 1.5:1
						Detail.	05/03/02	CV			
						Insp.					
09 65 329 3703	4-40 UNC	1				Stand.					
09 65 329 6703	4-40 UNC	2	31892	22/04/04	JH	HARTING EURL F-95972 Paris				TB 09 65 329 x70x	Blatt / Page 3
09 65 329 7703	4-40 UNC	3	29723	05/03/02	CV						
Part number	Screw lock thread	Performance level	Mod.	Dat.	Name					Sub.	



All Dim. in mm
Orig. Size DIN A 4

D-Sub, High temperature,
25 poles, male, straight,
with solder pins 2,9
and screw lock.

Moßstab/
Scale

1.5:1

Blatt / Page

3