



Part Number : [1064800103](#)

Product Description : Rack-Mount Fiber Enclosure,
4RU, 12 LGX Cassette / 288-Port Capacity

Series Number : 106406

Status : Active

Product Category : Fiber Optic Adapters




Documents and Resources

Drawings

[1064800103_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Contained per ED/71/2019 (16 July 2019)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

Part Details

General

Status	Active
Category	Fiber Optic Adapters
Series	106406
Description	Rack-Mount Fiber Enclosure, 4RU, 12 LGX Cassette / 288-Port Capacity
Component Type	Enclosure
Product Name	Fiber Enclosures and Cassettes
Type	LGX
UPC	191128975025

Electrical

Shielded	No
Shield Type	N/A

Physical

Alignment Sleeve	N/A
Angled Physical Contact (APC)	N/A
Color - Resin	N/A
Depth	312.00mm
Gender	N/A
Height	178.00mm
Material - Enclosure	Aluminum
Material - Housing	N/A
Mounting Style	Rack
Net Weight	0.001/g
Orientation	N/A
Panel Mount	N/A
Ports	288
Shutter	N/A

Width	434.00mm
-------	----------

Mates With / Use With

Use with Part(s)

Description	Part Number
LGX Cassette, 12 LC/PC-to-1 Male MTP/PC, Aqua	<u>1064810102</u>
LGX Cassette, 24 LC/PC-to-1 Male MTP/PC, Aqua	<u>1064810113</u>

This document was generated on Apr 28, 2026