
HellermannTyton

Technical data sheet

Article number:
161-41203 SBPE9D



Product Group	PE General Purpose Spiral Binding
Product Family	SBPE
Material	Polyethylene (PE)
Colour	Natural (NA)

Bundle Ø max.	100 mm
Bundle Ø min.	10 mm
Flammability	UL 94 HB
Nominal Ø	9 mm
Operating Temperature	-60 °C to +80 °C, intermittent +120 °C
Package Content	5 m
Package Content packed in	bag
Pitch (P)	12.5 mm
Wall (WT)	1.4 mm

HF ✓ RoHS ✓

created on 31. July 2026, 4:05 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.