

Energy storage - QUINT-BAT/24DC/ 7.2AH - 2866352

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Energy storage device, lead AGM, VRLA technology, 24 V DC, 7.2 Ah. Connection via pin cable lug, 14 mm.

Product Description

QUINT-BAT – energy storage with lead AGM technology for maximum buffer times.



Key Commercial Data

Packing unit	1 pc
GTIN	 4 017918 959753
GTIN	4017918959753
Weight per Piece (excluding packing)	6,640.000 g
Custom tariff number	85072080
Country of origin	China

Technical data

Dimensions

Width	164 mm
Height	156 mm
Depth	110 mm

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	0 °C ... 40 °C
Ambient temperature (storage/transport)	0 °C ... 40 °C

Input data

Energy storage - QUINT-BAT/24DC/ 7.2AH - 2866352

Technical data

Input data

Nominal input voltage	24 V DC
-----------------------	---------

Output data

Nominal output voltage	24 V DC
Output current I_{max}	50 A
Connection in parallel	yes, for increasing the buffer period
Connection in series	No
Output fuse	2x 25 A

General

IQ technology	no
Net weight	6 kg
Memory medium	7 Ah battery
Degree of protection	IP20
Protection class	III

Energy storage

Nominal capacity	7 Ah
------------------	------

Conformance/approvals


Shipbuilding approval	DNV GL (EMC A)
-----------------------	----------------

Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 3
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Block diagram



Classifications

eCl@ss

eCl@ss 10.0.1	27050403
---------------	----------

Energy storage - QUINT-BAT/24DC/ 7.2AH - 2866352

Classifications

eCl@ss

eCl@ss 11.0	27050403
eCl@ss 4.0	27040600
eCl@ss 4.1	27040600
eCl@ss 5.0	27040600
eCl@ss 5.1	27040600
eCl@ss 6.0	27040600
eCl@ss 7.0	27050403
eCl@ss 9.0	27050403

ETIM

ETIM 2.0	EC000382
ETIM 3.0	EC000382
ETIM 4.0	EC000357
ETIM 6.0	EC000357
ETIM 7.0	EC000357

UNSPSC

UNSPSC 6.01	30211510
UNSPSC 7.0901	39121011
UNSPSC 11	39121011
UNSPSC 12.01	39121011
UNSPSC 13.2	26111715
UNSPSC 18.0	26111715
UNSPSC 19.0	26111715
UNSPSC 20.0	26111715
UNSPSC 21.0	26111715

Approvals

Approvals

Approvals

GL / EAC / EAC

Ex Approvals

Approval details

Energy storage - QUINT-BAT/24DC/ 7.2AH - 2866352

Approvals

GL		https://approvalfinder.dnvgl.com/	TAA00002EW
EAC			EAC-Zulassung
EAC			RU*DE*08.B.01873/19

Accessories

Accessories

Assembly adapter

Mounting adapter - QUINT-ADAPTER/4 - 2866857

Assembly adapter for QUINT-BAT/24DC... on 35mm rail



Battery unit

Uninterruptible power supply replacement battery - UPS-BAT-KIT/PB/2X12V/7AH - 1283119



Replacement battery, VRLA-AGM, 2x12 V DC, 7 Ah

Uninterruptible power supply replacement battery - UPS-BAT-KIT-VRLA 2X12V/7,2AH - 2908234



Replacement battery for UPS-BAT/VRLA... energy storage

Energy storage - QUINT-BAT/24DC/ 7.2AH - 2866352

Accessories

Fuse

Fuse - FUSE 25A/32V ATOF - 2908366



Fuse, nominal current: 25 A, length: 19.1 mm, width: 5 mm, height: 18.8 mm
