


TWO CONDUCTOR CABLE, MODIFIED POLYESTER INSULATED,
600 VOLT, 120°C, LIGHTWEIGHT

The complete requirements for procuring the wire described herein shall consist of this document.

Component wire -
99M0111



Part Description	AWG Size	Outside Diameter (mm)		Maximum Weight (kg/km)
		Nom	Max	
99M0121-28-*/*	28	1.45	1.60	3.09
99M0121-26-*/*	26	1.75	1.90	5.97
99M0121-24-*/*	24	1.95	2.10	7.11
99M0121-22-*/*	22	2.25	2.40	10.09
99M0121-20-*/*	20	2.80	3.00	15.57
99M0121-18-*/*	18	3.30	3.50	21.42
99M0121-16-*/*	16	3.80	4.00	33.99
99M0121-14-*/*	14	4.50	4.70	42.64
99M0121-12-*/*	12	5.20	5.40	55.83

COLOUR CODE: The '*' in the part description shall be replaced by a standard colour code designator in accordance with Mil Std 681.
e.g. 99M0121-24-0/9 - cores Black and White insulation.

PERFORMANCE REQUIREMENTS: Shall meet the requirements of the issue in effect of TE Specification WCD 281

APPROVAL: Electronic sign off - no signatures will appear.