



Quality Products. Service Excellence.

Rack Mount Locking Storage Drawer *RDRW Series*

Load rated up to 145 lbs (66 kg)

Features



- Constructed of 14 and 16 gauge steel.
- Includes front plastic pull handle locking mechanism.
- The inside drawer width is 16.12" wide.
- Complete drawer with slides, hardware, lock & two keys.
- Available in 3 depths.
- Rear support brackets are included for all depths or can be supported from the rear rack rail.
- 6-Pack of 10-32 rack screws are included.
- Finished in textured RAL9005 black or RAL 7035 light gray powder coat. Complies with the Greenguard guidelines for indoor air quality.
- Up to 145 lbs (66 kg) **load rating** when mounted to two-pair/4-post rack rails.
 - Rated for 60 lbs (27 kg) when mounted one-pair/2-post rack rails.
- TAA-compliant for federal GSA schedule purchases within the USA.
- RoHS and REACH compliant.
- Manufactured in North America.

Accessories

- Hardware for Rack Mounting Solutions
- Rack Equipment Installation Tool
- Wing Knob Latch





Part No.	Part No.	Overall Dimensions			Usable Dimensions		Slide Travel	Rack Units	Weight Capacity
		Height	Width	Depth	Height	Depth			
RAL9005 Black	RAL 7035 Light Gray								
RDRW1900312BK1	RDRW1900312LG1	3.50	17.36	12.25	2.89	11.32	12.00	2U	145 lbs (65.8 kg)
RDRW1900512BK1	RDRW1900512LG1	5.25	17.36	12.25	4.64	11.33	12.00	3U	145 lbs (65.8 kg)
RDRW1900712BK1	RDRW1900712LG1	7.00	17.36	12.25	6.39	11.33	12.00	4U	145 lbs (65.8 kg)
-	RDRW1900812LG1	8.75	17.36	12.25	8.14	11.33	12.00	5U	145 lbs (65.8 kg)
RDRW1900316BK1	RDRW1900316LG1	3.50	17.36	16.25	2.89	15.33	16.00	2U	129 lbs (58.5 kg)
RDRW1900516BK1	RDRW1900516LG1	5.25	17.36	16.25	4.64	15.33	16.00	3U	129 lbs (58.5 kg)
RDRW1900716BK1	RDRW1900716LG1	7.00	17.36	16.25	6.39	15.33	16.00	4U	129 lbs (58.5 kg)
RDRW1900816BK1	RDRW1900816LG1	8.75	17.36	16.25	8.14	15.33	16.00	5U	129 lbs (58.5 kg)
-	RDRW1901216LG1	12.25	17.36	16.25	11.64	15.33	16.00	7U	129 lbs (58.5 kg)
RDRW1900322BK1	RDRW1900322LG1	3.50	17.36	22.25	2.89	21.33	22.00	2U	107 lbs (48.5 kg)
RDRW1900522BK1	RDRW1900522LG1	5.25	17.36	22.25	4.64	21.33	22.00	3U	107 lbs (48.5 kg)
RDRW1900722BK1	RDRW1900722LG1	7.00	17.36	22.25	6.39	21.33	22.00	4U	107 lbs (48.5 kg)
RDRW1900822BK1	RDRW1900822LG1	8.75	17.36	22.25	8.14	21.33	22.00	5U	107 lbs (48.5 kg)
RDRW1901222BK1	RDRW1901222LG1	12.25	17.36	22.25	11.64	21.33	22.00	7U	107 lbs (48.5 kg)

Qty Included	Description	Replacement Part No.
1	Drawer	
2	Keys for lock	
8	10-32 x 0.625in screw	
2	Rear drawer support bracket	
4	8-32 Keps nut	
1	Assembly and installation instructions	

Tags: Lockable Storage Drawer

Data subject to change without notice

