



REVISIONS			
REV	DESCRIPTION, ECN, EAR NO.	DATE	APP'D
F	PROPOSAL DRAWING (EAR 14940)	JUN04/21	M.P.
G	PROPOSAL DWG - REV PER EAR 14940	NOV12/21	M.P.





APPLICATION VIEW
DOME SHOWN ASSEMBLED
TO 84mm ANSI C136.41 BASE
SCALE 3:2






ORDERING CODE: FLB-C80-XX X-001

HEIGHT

XX	'H'	'Y'
35	35 mm	5.5 mm
50	50 mm	20.5 mm
60	60 mm	30.5 mm
75	75 mm	45.5 mm
10	95 mm	65.5 mm
13	130 mm	100.5 mm

COLOUR
1 = GREY
2 = CLEAR (TRANSPARENT)
3 = RED
4 = BLACK
5 = WHITE
6 = TRANSLUCENT
7 = YELLOW



NOTES:

1. MATERIAL: POLYCARBONATE
   - UL94-5VA FLAMMABILITY RATING
   - COLOUR AS PER ORDERING CODE
   - RoHS COMPLIANT PER EU DIRECTIVE 2011/65/EU & AMENDMENTS
2. DESIGNED FOR USE WITH AMPHENOL ANSI C136.41 84mm BASES, CONTACT AMPHENOL FOR PRODUCT OFFERINGS.

AMPHENOL CANADA CORP. RoHS COMPLIANT 2011/65/EU RECAST

UNLESS SPECIFIED OTHERWISE	DRAWN	S.MUGAN	JUL06/20
PRIMARY UNITS MILLIMETERS	CHECKED	A.GREEN	JUL06/20
SECONDARY	M.E. APP'D		
REFERENCE IN PARENTHESES	Q.A. APP'D		
GENERAL TOLERANCES	DWG APPR.		
1 DECIMAL PLACE	ENG. REL. NO.		
2 DECIMAL PLACES ± 0.30	REF.		
3 DECIMAL PLACES	THIRD ANGLE PROJECTION	DO NOT SCALE DRAWING	
ANGULAR DEGREES			

Amphenol Canada Corp.
Commercial Products

FLB SERIES, DOME COVER
FOR ANSI C136.41 84mm BASES,
HEIGHT & COLOUR OPTIONS,
RoHS COMPLIANT

DWG. NO. P-FLB-C80-XXX-001 REV G

CODE ID NO. 03554 | DWG SIZE: X | SCALE: 1:1 | SHEET 1 OF 1

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.

Downloaded from Arrow.com.