**Part Number :** 1301530182
**Product Description :** Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Flying Leads, 30A, 240V, 0.61m (2.0') (2.0') Cord Length
**Series Number :** 130153
**Status :** Active
**Product Category :** Power Distribution
**Engineering Part Number :** 30053-0M



## Documents and Resources

### Drawings

1301530182_sd.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Reviewed per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Not Reviewed per IEC 61249-2-21 |
| REACH SVHC | Not Reviewed per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Power Distribution |
| Series | 130153 |
| Description | Super-Safeway In-Line Industrial GFCI, Portable, Single Phase, Manual Reset, Flying Leads, 30A, 240V, 0.61m (2.0') (2.0') Cord Length |
| Enclosure Rating | NEMA 6P |
| NEMA Configuration | N/A |
| Product Name | Super-Safeway |
| Type | GFCI Industrial Duty, Single Phase |
| UPC | 78678889719 |

### Agency

| | |
|---|---|
| UL | E66308 |

### Electrical

| | |
|---|---|
| Current - Maximum per Contact | 30.0A |
| GFCI | Yes-In-line |
| GFCI Reset | Manual |
| Ground Continuity Monitor | No |
| Open Neutral Relay | Yes |
| Voltage - Maximum | 240V |

### Physical

| | |
|---|---|
| Cord Diameter | N/A |
| Cord Grip Body Size | N/A |
| Cord Length | N/A |

Downloaded from Arrow.com.

| | |
|---|---|
| Cord Type | 10/3 SJEOOW |
| Feed-Thru | No |
| Flip Lid | No |
| Material - Housing | Nylon |
| Mounting Style | Portable |
| Net Weight | 913.080/g |
| Number of Receptacles | 0 |
| Packaging Type | Bag |
| Receptacle Type | N/A |



Downloaded from Arrow.com.