



Part Number : 1300940514

Product Description : Bus-Drop Support Grip, Locking Bale, Cable Diameter 10.41-14.22mm (.410-.560"), Approximate Break Strength 498.95kg (1100 lbs)

Series Number : 130094

Status : Active

Product Category : Cable Grips

Engineering Number : 36584



Documents & Resources

Drawings

Drawing 1300940514_sd.pdf

Packaging Design Drawing PK-130227-004-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)4144-DC (27 June 2024)
EU RoHS	Not Reviewed per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Part Details

General

Status	Active
Category	Cable Grips
Series	130094
Description	Bus-Drop Support Grip, Locking Bale, Cable Diameter 10.41-14.22mm (.410-.560"), Approximate Break Strength 498.95kg (1100 lbs)
Product Family	Support Grips
Product Name	Bus-Drop
Type	Support Grip
UPC	78678836584

Agency

CSA	LR32159
UL	E76954

Physical

Approximate Break Strength	498.95kg (1100 lbs)
Bale Length	0.305m (12.00")
Body Style	Straight
Cable Diameter	10.41-14.22mm (.410-.560")
Color - Grommet	N/A
Eye Type	Locking Bale
Gender	N/A
Material - Body	N/A
Material - Grip	Galvanized Steel
Mesh Length	0.127m (5.00")
Net Weight	57.137/g
Number of Holes	N/A
O-Ring	N/A
Thread Size	N/A

This document was generated on Sep 30, 2024