Part Number : 02065108
Product Description : 1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 24-18 AWG, Reel
Series Number : 1561
Status : Active
Product Category : Crimp Terminals
Engineering Part Number : 1561-(P228)
Packaging Alternative : 02065109 (Bag)



Documents and Resources

Drawings

002065108_sd.pdf

15610000-PK-000.pdf

STEP AP242

SOLIDWORKS

Creo

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Terminals
Series	1561
Description	1.57mm Diameter, Standard .062" Pin and Socket Crimp Terminal, Female, with Selective Gold (Au) Plated Brass Contact, 24-18 AWG, Reel
Application	Power, Wire-to-Wire
Product Name	Standard .062"
UPC	800753615755

Physical

Gender	Female
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.080/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.52-3.05mm
Wire Size (AWG)	18, 20, 22, 24

Downloaded from Arrow.com.

Wire Size mm^2	N/A

Application Tooling

Global

Description	Part Number
Insertion Tool for Standard .062" Diameter Male and Female Terminals	11020001
Extraction Tool for Standard .062" and Standard .062"+ Pin and Socket Terminals	11030002
Terminator Die	11402004
ServiceGrade Hand Crimp Tool for Field Repair Only, 24-14 AWG	638111000
Hand Crimp Tool for Standard 1.57mm Pin and Socket Crimp Terminals, 24-18 AWG	638191300
Mini-Mac Applicator for Standard .062" Pin and Socket Terminals, for 24-18 AWG Wire with Insulation Diameter 1.52-3.05mm	638914000

Downloaded from Arrow.com.