

Part Number : 194130096
Product Description : Solderless Terminals Kit, HVAC Electrical Terminal Assortment, 450 Pieces
Series Number : 19413
Status : Active
Product Category : Kits
Engineering Part Number : KIT-MX1

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Downloaded from Arrow.com.

Part Details

General

Status	Active
Category	Kits
Series	19413
Description	Solderless Terminals Kit, HVAC Electrical Terminal Assortment, 450 Pieces
Comments	Includes 25 of each part number in the kit. See Kit Components below for links to included parts.
Component Type	Kit
Kit Component Parts	Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 16-14 AWG, Tab 6.35mm, Carton, Krimptite Quick Disconnect, Female, Steel Flag, 483°C (900° F), 16-14 AWG, InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton, InsulKrimp Quick Disconnect, Female, for 10-12 (5.00-3.30mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton, InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 16-14 AWG, Blue Insulator, Loose, Carton, Krimptite Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5), Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), InsulKrimp Ring Tongue Terminal for 16-14 AWG, Vinyl, InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 27.40mm, Yellow, Carton, InsulKrimp Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Blue, Length 20.90mm, Carton, InsulKrimp Block Spade Tongue Terminal for

Downloaded from Arrow.com.

	12-10 AWG Wire, Stud Size 10 (M5), Length 27.31mm, Carton, InsulKrimp Butt Splice for 22-18 AWG Wire, Carton, InsulKrimp Butt Splice for 16-14 AWG Wire, Carton, InsulKrimp Butt Splice for 12-10 AWG Wire, Carton, Closed-End Insulated Splice for 22-14 AWG Wire, Clear, Closed-End Insulated Splice for 18-10 AWG Wire, InsulKrimp Fully Insulated Coupler, Female, for 16-14 AWG Wire, Box, Carton, Three Way Connector, Dual Male, Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated, Carton
Product Name	Solderless Terminals Kit
UPC	191128415033

Physical

Circuits (Loaded)	N/A
Depth	45.00mm
Length	280.00mm
Width	172.00mm

Kit Component Parts

Description	Part Number
Krimptite Quick Disconnect, Female, Steel, 483°C (900° F), 16-14 AWG, Tab 6.35mm, Carton	192030390
Krimptite Quick Disconnect, Female, Steel Flag, 483°C (900° F), 16-14 AWG	192030375
InsulKrimp Quick Disconnect, Female, for 14-16 (2.00-1.30mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton	190170037
InsulKrimp Quick Disconnect,	190170047

Downloaded from Arrow.com.

Female, for 10-12 (5.00-3.30mm^2) Wire, Box, Tab 6.35 x 0.81mm, Carton	
InsulKrimp Piggyback Quick Disconnect, Tab 6.35 x 0.81mm, 16-14 AWG, Blue Insulator, Loose, Carton	190110037
Krimptite Ring Tongue Terminal for 16-14 AWG Wire, Stud Size 10 (M5)	192030388
Krimptite Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5)	192030389
InsulKrimp Ring Tongue Terminal for 16-14 AWG, Vinyl	190540119
InsulKrimp Ring Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 27.40mm, Yellow, Carton	190700123
InsulKrimp Spade Tongue Terminal for 16-14 AWG Wire, Stud Size 8 (M4), Blue, Length 20.90mm, Carton	191300045
InsulKrimp Block Spade Tongue Terminal for 12-10 AWG Wire, Stud Size 10 (M5), Length 27.31mm, Carton	191310002
InsulKrimp Butt Splice for 22-18 AWG Wire, Carton	191540004
InsulKrimp Butt Splice for 16-14 AWG Wire, Carton	191540015
InsulKrimp Butt Splice for 12-10 AWG Wire, Carton	191540028
Closed-End Insulated Splice for 22-14 AWG Wire, Clear	191600012
Closed-End Insulated Splice for 18-10 AWG Wire	191600190
InsulKrimp Fully Insulated Coupler, Female, for 16-14 AWG Wire, Box, Carton	190050005
Three Way Connector, Dual Male,	190430010

Downloaded from Arrow.com.

Single Female Quick Disconnect Adapter, 6.35 x 0.81mm Tab Size, Non-Plated, Carton	

Downloaded from Arrow.com.