

5

4

3

2


1

D


C


B

A



Max wire ϕ 1,05 mm



						Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 25 poles, male, straight, turned solder buckets, holes	Maßstab/ Scale	
						Detail.	18/07/01			AF	1.5:1
						Insp.					
						Stand.					
09 67 025 5615 050	3.1 ^{+0,1}	S4				HARTING EURL F-95972 Paris			TB 09 67 025 56xx Sub.		
09 67 025 5615	3.1 ^{+0,1}	PL2									Blatt/ Page 1 / 2
09 67 025 5604	3.1 ^{+0,1}	PL3	36189	08/11/10	SC						
Part number	ϕ hole	Performance level	Mod.	Dot.	Name						