

Home: >

Part Number: 76160-3076

Image not available

Status: Contact Molex
Series: [76160](#)
Category: Molex Parts

CHECK DISTRIBUTOR INVENTORY

[Add to My Parts](#)

Go to **Part Detail**▼

Series image - Reference only

Specifications & Other Documents:

Documents not available online

Note - Please disable browser pop-up blockers to view documents on [www.molex.com](#)

Product Environmental Compliance

Questions on Product Environmental Compliance? Email productcompliance@molex.com

EU ELV:Not Relevant
EU RoHS:Not Relevant
EU RoHS Phthalates:Not Relevant
China RoHS:
REACH SVHC:Not Relevant
Low-Halogen Status:Not Relevant



Product Compliance Statement

Application Tooling [FAQ](#)

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling
[Check our list of old tooling that used to be available for this part](#)

Part Detail

COLLAPSE ALL

▼ General

Status	Contact Molex
Category	Molex Parts
Series	76160
UPC	887191898384

▼ Physical

Flammability	94V-0
Net Weight	10.649/g

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number. [Click here to visit the UL Database](#)

UL	E29179
----	--------

▼ Material Info

PRODUCTS

Antennas
Application Tooling
Cable Assemblies
Connected Lighting

QUICK LINKS

Company Information
Contact Molex
Cross-Reference
Koch Industries

RESOURCES

California Supply Chains Act
Compliance
ecocare
Feedback | Help

STAY CONNECTED



[Connectors](#)

[Copper Flex](#)

[Electrical Products](#)

[Industrial Automation](#)

[Membrane Switches](#)

[Optical Solutions](#)

[PCB Assemblies](#)

[Industries](#)

[Literature](#)

[Press Room / Press Releases](#)

[Product Index](#)

[Sitemap](#)

[Jobs](#)

[Legal | Trademarks](#)

[Mobile Site](#)

[Supplier Portal](#)

[Privacy Policy](#)

[Tradeshows](#)



© Copyright 2017