




**Part Number :** [638320600](#)  
**Product Description :** Mini-Mac Applicator Air Feed for Power 60 Amp Crimp Terminals, 6 AWG  
**Series Number :** 207127  
**Status :** Active  
**Product Category :** Applicators and Crimp Modules



## Documents & Resources

**Tooling Specifications**  
[ATS-638013501-001.pdf](#)  
[ATS-638320600-001.pdf](#)

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Not Reviewed per EU 2015/863

### Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Applicators and Crimp Modules
Series	207127
Description	Mini-Mac Applicator Air Feed for Power 60 Amp Crimp Terminals, 6 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Automatic, Semi-Automatic
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Mini-Mac
Tool Type	Applicator
UPC	884982064577
Warranty Disclaimer	<p>CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>

### Physical

Net Weight	1.000/g
------------	---------

---

### Use with Part(s)

Description	Part Number
-------------	-------------

TM-2000 Universal Press	<u>638008300</u>
TM-2000 Universal Press (Europe 220V)	<u>638008400</u>
TM-3000 Universal Crimp Press, 120AC 50/60Hz, Used for product up to 10 AWG	<u>638017200</u>
TM-3000 Universal Crimp Press, 220AC 50/60Hz, Used for product up to 10 AWG	<u>638017300</u>
TM-4000 Universal Crimp Press, 240AC 50/60Hz, Used for product up to 4 AWG	<u>638017600</u>
Use With	Most Industry Standard Presses or Wire Process Machines

---

### Applicable Parts

Description	Part Number
EXTreme Guardian High Power Terminal, 6 AWG Crimp, 0.76µm Gold (Au)	<u>468190013</u>

---

This document was generated on Feb 27, 2025