

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039000047

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Female Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass, 22-28 AWG, Bag

- Documents:
- Drawing (PDF)

Product Specification 55560002-PS-CH-000 (PDF)

Product Specification 55560002-PS-ES-000 (PDF)

Product Specification 55560002-PS-SK-000 (PDF)

Product Specification PS-5556-001-001 (PDF)

Product Specification PS-5556-002-001 (PDF)

Application Specification 55560001-AS-000 (PDF)

Packaging Specification PK-5556-003-001 (PDF)

Test Summary 55560000-TS-000 (PDF)

Test Summary 55560010-TS-000 (PDF)

Test Summary TS-5556-002-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	5556
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Mini-Fit Family Power Connectors
Packaging Alternative	39000046 (Reel)
Product Name	Mini-Fit
Taxonomy	Crimp Terminals
UPC	800753727212

Physical	
Durability (mating cycles max)	30
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.123/g
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90-1.80mm
Wire Size AWG	22, 24, 26, 28
Wire Size mm²	N/A

Electrical	
Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info	
Engineering Number	5556T2L

Reference - Drawing Numbers	
Application Specification	55560001-AS-000
Packaging Specification	PK-5556-003-001
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	55560000-SD-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2022)4187-DC (10 June 2022)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

5556 Series

Use With

Mini-Fit Jr. Receptacle Housing 5557

Mini-Fit BMI Slide and Lock Panel Mount 44516
Mini-Fit BMI Panel Mount Receptacle Housing
 42474 , 43760

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Mini-Fit Jr. Terminals PremiumGrade Hand	11030044638191000
Crimp Tool for Mini-Fit Jr. Male and Female Terminals, 22-28 AWG	
Japan	

Description	Product #
Hand Extraction Tool	<u>570316000</u>
Handtool - Straight Action	<u>570385300</u>
Hand Crimp Tool	<u>570645000</u>

This document was generated on 08/26/2022

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION