




- * **ⓄⓄ** Important Dimension To Check.
- * Waterproof Rate: IP68(Mated)
In 1 meter water within 24 hours
- * Working Voltage Rating:
Power: AC/DC 300V
Data: DC 30V
- * Working Current:
Power: 10A
Data: 05A
- * Housing: Nylon+GF, Black.
- * Pin: Copper Alloy, Gold Plated.
- * O-Ring: Silicone, Gray.
- * Cable: UL21996 16AWG*2C+(26AWG*2P+AL/MY)
+F+AL/MY, PVC Jacket, OD=9.3, Black.
- * Cable Length Tolerance: 01M: ±40mm
02M~05M: ±60mm
06M~10M: ±100mm
11M~30M: ±200mm
31M~99M: ±500mm

Amphenol LTW

安費諾亮泰企業股份有限公司

ITEM NO	DRAWN BY	DATE
	Spring	2016-05-07
DWG NO	CHECKED BY	DATE
BBD-06AFFM-QL8FXX	Fisher	2016-05-07
CUSTOMER	APPROVED BY	DATE
ALTW	Kevin	2016-05-07