



NC3FD-H-B

3 pole female receptacle, horizontal PCB mount, black metal housing, gold contacts

Universal D-size metal body XLR panel mount series for pcb mount applications. Insert is removable from shell for ease assembling. UL recognized component.

Features & Benefits

- ✓ D-shape metal shell
- ✓ Optimal RF protection using 3 shield contacts
- ✓ Insert is removable from rear of connector and locked into place by internal latch - permitting assembling and testing of pcb before assembling into housing
- ✓ Front or rear panel mount

Technical Information

Product	
Title	NC3FD-H-B
Connection Type	XLR
Gender	female

Electrical

Capacitance between contacts	$\leq 4 \text{ pF}$
Contact resistance	$\leq 5 \text{ m}\Omega$
Dielectric strength	1,5 kVdc
Insulation resistance	$> 10 \text{ G}\Omega$ (initial)
Rated current per contact	6 A
Rated voltage	$< 50 \text{ V}$

Mechanical

Insertion force	$\leq 20 \text{ N}$
Withdrawal force	$\leq 20 \text{ N}$
Lifetime	> 1000 mating cycles
Wiresize	
Wiring	Horizontal PCB mount
Locking device	Latch lock
Mounting direction	Rear mounting
Chassis shape	D

Material	
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Bronze (CuSn6)
Insert	PA66
Locking element	Steel Ck67
Locking element plating	Nickel
Shell	Zinc diecast (ZnAl4Cu1)
Shell plating	Black KTL

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 40
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C