

Part Number : 2153412203
Product Description : Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Gold (Au) Plating, 225.00mm Length, 20 AWG, Red
Series Number : 215341
Status : Obsolete
Product Category : Power and Signal Cable Assemblies

Documents and Resources

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Obsolete

Downloaded from Arrow.com.

Part Details

General

Status	Obsolete
Category	Power and Signal Cable Assemblies
Series	215341
Description	Pre-Crimped Lead Mini-Fit Jr. Female-to-Pigtail, Gold (Au) Plating, 225.00mm Length, 20 AWG, Red
Application	Wire-to-Board, Wire-to-Wire
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Mini-Fit Jr. Term-to-Pigtail
Keyword	Pre-Crimped Leads
Product Name	Mini-Fit Jr.
UPC	193264559763

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Physical

Cable Length	225.00mm
Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Red
Gender	Female-Pigtail
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	2.951/g
Packaging Type	Bag
Single Ended	Yes
Termination Interface Style	Crimp or Compression
Wire/Cable Type	UL 1015
Wire Size (AWG)	20

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Use with Part(s)

Description	Part Number
Mini-Fit Jr. Receptacle Housings	5557
Mini-Fit BMI Dual Row Receptacle Housings	44516
Mini-Fit BMI Dual Row Receptacle Housings	42474
Mini-Fit BMI Dual Row Receptacle Housings	43760

Obsolete

Downloaded from Arrow.com.