Part Number : 1205000345
Product Description : Micro-Change (M12) Single-Ended Cordset, 4 Poles, L-Coded, Male (Straight) to Pigtail, 16 AWG, Black TPU WSOR Cable, 5.0m (16.4') Length
Series Number : 120500
Status : Active
Product Category : Industrial Cable Assemblies
Engineering Part Number : L0P4006B43M050



Documents and Resources

Drawings

1205000345_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3 per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2025)7771-DC (04 Feb 2026) SCIP:5e7f52a6-d6dd-4809-9519-e3ec076d1b41
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Downloaded from Arrow.com.

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

UKCA - Declaration of Conformity

CE - Declaration of Conformity

Part Details

General

Status	Active
Category	Industrial Cable Assemblies
Series	120500
Description	Micro-Change (M12) Single-Ended Cordset, 4 Poles, L-Coded, Male (Straight) to Pigtail, 16 AWG, Black TPU WSOR Cable, 5.0m (16.4') Length
IP Rating	IP67
Product Name	Micro-Change (M12)
Type	Single Ended
UPC	196823152078

Agency

UL	E152210

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	63V

Physical

Cable Diameter	7.90mm (.311")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Micro-Change (M12)
Connector End B	Pigtail
Coupling Style	Threaded

Downloaded from Arrow.com.

Gender	Male-Pigtail
Keyway	L-Coded
LED Indicator	None
Material - Cable Jacket	WSOR TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	543.500/g
Orientation	Straight to Pigtail
Poles	4
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16

Downloaded from Arrow.com.