



Part Number : 1301120258

Series Number : 130112

Product Category : Portable Lighting Accessories

Product Description : Replacement Guard for 5030, 10 Pack

Status : Active

Engineering Number : STR105

Product Environment Compliance

Compliance

| | |
|--------------------|---|
| GADSL/IMDS | Not Relevant |
| China RoHS | Not Relevant |
| EU ELV | Not Reviewed per 2000/53/EC |
| Low-Halogen Status | Not Relevant |
| REACH SVHC | Not Reviewed per D(2023)8585-DC (23 Jan 2024) |
| EU RoHS | Not Reviewed per EU 2015/863 |

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

| | |
|-------------|-------------------------------------|
| Status | Active |
| Category | Portable Lighting Accessories |
| Series | 130112 |
| Description | Replacement Guard for 5030, 10 Pack |

| | |
|--------------------|----------------------|
| NEMA Configuration | N/A |
| Product Family | Lighting Accessories |
| Product Name | Woodhead |
| Type | Accessory |
| UPC | 78172538191 |

Electrical

| | |
|-----------------------------|-----|
| Lamp Wattage - Maximum | N/A |
| On/Off Switch | N/A |
| Voltage (Fixture) - Maximum | N/A |

Physical

| | |
|-------------------------|-------------------|
| Bulb Type | N/A |
| Cord Length - Primary | N/A |
| Cord Length - Secondary | N/A |
| Depth | 138.43mm (5.450") |
| Duty | Commercial |
| Guard Included | Yes |
| Guard Type | Polypropylene |
| Height | 180.98mm (7.125") |
| Lamp Type | A21 |
| Length | N/A |
| Material - Guard | Polypropylene |
| Outlet | N/A |
| Packaging Type | Carton |

This document was generated on Jul 03, 2024