

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-MONTYWELL REGULATOR COMPANY
FREEPORT, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

(M) DT-2R4-B6
ISSUE 2

REPLACES

RELEASE NO.

CHECK

CHECK

CHECK

2
D
S


DT-2R4-B6

**DRAWING
NUMBER**

9	✖
✖	✖
✖	ISSUE
✖	

REVISIONS

A	CO15451	L S D
	28 JUN 61	
B	CO17707	R E R
	14 MAR 63	
C	CO17725	L S D
	25 JUN 63	
D	CO19276	M B F
	12 JUNE 64	
E	CO-30659	S R H
31	CO MAY 72	
F	CO37528	C J H
31	AUG 76	
G	CO 39046	G A S
16	SEP 77	



NOTE --

▲-MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF
 .139 MAX DIA ON $1.000 \pm .002$ CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS

OPERATING FORCE - - - - - 12-20 0Z

RELEASE FORCE - - - - - (B) 1 OZ MIN

DIFFERENTIAL TRAVEL — — — — .04 0 — .060

OVERTRAVEL- - - - - .015 MIN

ELECTRICAL DATA

CONTACT ARRANGEMENT
D.P.D T

UNDERWRITERS' LAB. INC. LISTED RATING
-L59- 10 A-125 OR 250 VAC
0.3 A-125 VDC ; 0.15 A-250 VDC



SCALE FULL

DO NOT SCALE PRINT

**UNLESS OTHERWISE
SPECIFIED**

DIMENSIONS ARE IN INCHES

TOLERANCES ARE:

ONE PLACE	(.0)	$\pm .030$
TWO PLACE	(.00)	$\pm .015$
THREE PLACE	(.000)	$\pm .008$
ANGLES		$\pm$

WEIGHT