



Part Number : [731000195](#)
Product Description : BNC Jack, Straight, Bulkhead
Receptacle, Solder Cup Contact, Brass Body, Nickel (Ni)
Plated, Bulk Bag, 50 Ohms
Series Number : 73171
Status : Active
Product Category : RF / Coaxial Connectors



Documents & Resources

Drawings

[731000195 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Contains Lead per D(2024)6225-DC (07 Nov 2024)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C

- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	RF / Coaxial Connectors
Series	73171
Description	BNC Jack, Straight, Bulkhead Receptacle, Solder Cup Contact, Brass Body, Nickel (Ni) Plated, Bulk Bag, 50 Ohms
Application	RF
Comments	Solder Pot
Product Name	BNC
Style	Panel
Type	Miniature
UPC	800753686236

Electrical

Frequency	2 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level

Physical

Cable Attachment	Solder
Gender	Jack
Keying to Mating Part	N/A
Net Weight	7.824/g
Orientation	Straight

Packaging Type	Bag
Panel Mount	Yes
Panel Mount Method	Bulkhead
PCB Mounting	N/A
Reverse Polar	No
Wire/Cable Type	1.32mm Coaxial max.

Solder Process Data

Lead-Free Process Capability	N/A
------------------------------	-----

This document was generated on Sep 29, 2025