

# UC-WMCO 4,9 (12X5) - Conductor marker



0827733

<https://www.phoenixcontact.com/us/products/0827733>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Conductor marker, Sheet, white, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID COLOR, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 3.6 ... 4.9 mm, lettering field size: 12 x 5 mm, Number of individual labels: 24

## Your advantages

- The markers, which are supplied in uniform sheets, can be printed onto quickly and easily using the BLUEMARK printing systems
- The UC-WMCO ... UniCard labeling range includes thread-on markers for the subsequent labeling of conductors by simply sliding them on using the UC-WMCO ... TOOL
- The format automatically ensures printing with a high degree of positioning accuracy
- Secure tight fit even in the event of vibrations
- Large-surface labeling option in a space-saving design
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all UniCard markers according to your specifications

## Commercial data

Item number	0827733
Packing unit	5 pc
Minimum order quantity	5 pc
Sales key	BG10
Product key	BG2217
Catalog page	Page 200 (C-3-2019)
GTIN	4046356445610
Weight per piece (including packing)	11.48 g
Weight per piece (excluding packing)	11.46 g
Customs tariff number	39269097
Country of origin	PL

# UC-WMCO 4,9 (12X5) - Conductor marker



0827733

<https://www.phoenixcontact.com/us/products/0827733>

## Technical data

### Product properties

Product type	Conductor marking
Type	Card form

### Data management status

Article revision	03
------------------	----

### Marking

Number of individual labels	24
Number of individual labels per row	6
Identification technology	UV LED technology

### Dimensions

Width	5 mm
Text field width	12.00 mm
Text field height	5.00 mm
Length	12 mm

### External dimensions

Outside diameter	3.6 mm ... 4.9 mm
------------------	-------------------

### Material specifications

RoHS compliant	yes
Color	white
Material	PA
Flammability rating according to UL 94	V2
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	120 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 2
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 2
Components	free from silicone and halogen

### Cable/line

External cable diameter	3.6 mm ... 4.9 mm
-------------------------	-------------------

### Environmental and real-life conditions

#### Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

#### UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed

# UC-WMCO 4,9 (12X5) - Conductor marker



0827733

<https://www.phoenixcontact.com/us/products/0827733>

Test duration	96 h
---------------	------

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropyl [CAS No. 67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

## Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

## Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

## Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

## Mounting

Mounting type	slide-on
---------------	----------

# UC-WMCO 4,9 (12X5) - Conductor marker



0827733

<https://www.phoenixcontact.com/us/products/0827733>

## Classifications

### ECLASS

ECLASS-11.0	27281102
ECLASS-12.0	27281102
ECLASS-13.0	27281102

### ETIM

ETIM 9.0	EC001530
----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# UC-WMCO 4,9 (12X5) - Conductor marker



0827733

<https://www.phoenixcontact.com/us/products/0827733>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

# UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## Accessories

### BLUEMARK ID - Printer

1003334

<https://www.phoenixcontact.com/us/products/1003334>



Monochrome printer with UV inkjet technology and integrated "MARKING system app" identification software. 7" touch color display for printing plastic labels in UC, UCT, US, and UM format, as well as metal labels.

---

### BLUEMARK ID COLOR - Printer

1002329

<https://www.phoenixcontact.com/us/products/1002329>



CMYK multicolor printer with UV inkjet technology, with integrated "MARKING system app" identification software, 7" touch color display for printing plastic labels in UC, UCT, and UM format, as well as metal labels.

## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>




## PLOTMARK - Marking plotter

0804499

<https://www.phoenixcontact.com/us/products/0804499>

Marking plotter for the entire portfolio of UC marking materials and materials in sheet and strip format.




---

## CMS-P1-PLOTTER - Marking plotter

5144615

<https://www.phoenixcontact.com/us/products/5144615>

Marking plotter, weight: 8 kg, length: 0.66 m, width: 440 mm, height: 125 mm, color: silver



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



### BM ID-CARTR. BK - Ink cartridge

1044345

<https://www.phoenixcontact.com/us/products/1044345>



Replacement UV fluid, 23 ml, color: black

---

### BM ID-CARTR. CY - Ink cartridge

1044346

<https://www.phoenixcontact.com/us/products/1044346>



Replacement UV fluid, 23 ml, color: cyan



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## BM ID-CARTR. YE - Ink cartridge

1044348

<https://www.phoenixcontact.com/us/products/1044348>



Replacement UV fluid, 23 ml, color: yellow

---

## BM ID-CLEANING CARTR. - Cleaning cartridge

1044350

<https://www.phoenixcontact.com/us/products/1044350>



Replacement cleaning cartridge

## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## BLUEMARK CLED-FLUID-CARTR. - Ink cartridge

5146662

<https://www.phoenixcontact.com/us/products/5146662>

Cartridge, for replacement, 20 ml UV color, black, including cleaning cartridge



---

## BLUEMARK FLUID-CARTRIDGE - Ink cartridge

5147421

<https://www.phoenixcontact.com/us/products/5147421>

Cartridge, for replacement, 28 ml UV color, black including cleaning cartridge



# UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## CMS-DISPOSABLE-PEN 0,25 TR - Marker pen

5146685

<https://www.phoenixcontact.com/us/products/5146685>

Disposable pen, incl. adapter, integrated ink cartridge and pen station, writing thickness: 0.25 mm



---

## CMS-DISPOSABLE-PEN 0,35 TR - Marker pen

5146686

<https://www.phoenixcontact.com/us/products/5146686>

Disposable pen, incl. adapter, integrated ink cartridge and pen station, writing thickness: 0.35 mm



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## CMS-INK-TR-C5 - Ink cartridge

5146684

<https://www.phoenixcontact.com/us/products/5146684>

Ink cartridge, special black ink, 5 cartridges of 1 ml each, for high demands



---

## CMS-PEN 0,25 - Marker pen

5067815

<https://www.phoenixcontact.com/us/products/5067815>

Marker pen, incl. adapter, ink tank and reservoir, 0.25 mm nib



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## CMS-PEN 0,35 - Marker pen

5067828

<https://www.phoenixcontact.com/us/products/5067828>

Marker pen, incl. adapter, ink tank and reservoir, 0.35 mm nib



---

## CMS-PEN 0,50 - Marker pen

5067831

<https://www.phoenixcontact.com/us/products/5067831>

Marker pen, incl. adapter, ink tank and reservoir, 0.5 mm nib



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## CMS-R-FLUID-TR - Cleaning fluid

5146750

<https://www.phoenixcontact.com/us/products/5146750>

Cleaning fluid, 30 ml, for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...



---

## CMS-R-FLUID-TR-C2 - Cleaning cartridge

5146752

<https://www.phoenixcontact.com/us/products/5146752>

Cleaning cartridges with replacement sealing caps, 2 cartridges with 10 ml cleaning fluid each and 2 caps for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...



## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## BM ID-MAG20 - Magazine

1044356

<https://www.phoenixcontact.com/us/products/1044356>



Infeed magazine for accommodating a max. of 20 UniCard sheets

---

## BM ID-MAG40 - Magazine

1044357

<https://www.phoenixcontact.com/us/products/1044357>



Infeed magazine for accommodating a maxi. of 40 UniCard sheets

## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## P1 UC-MAG 7 - Magazine

5146568

<https://www.phoenixcontact.com/us/products/5146568>

Magazine, for CMS-P1-PLOTTER and PLOTMARK, for accommodating: UC-WMCO...



---

## CMS-R-SET-TR - Cleaning set

5146751

<https://www.phoenixcontact.com/us/products/5146751>

Cleaning set, consisting of: 1x cleaning cup, 2x cleaning cartridges with 10 ml cleaning fluid each and 2x replacement sealing caps for the CMS-PEN ... and CMS-DISPOSABLE-PEN ...





## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



### UC-WMCO TOOL SET - Alignment tool for cable markers

0827807

<https://www.phoenixcontact.com/us/products/0827807>



Alignment tool for cable markers, orange, unlabeled, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 1.6 ... 7 mm

---

### UC-WMCO 3,6 TOOL - Alignment tool for cable markers

0827804

<https://www.phoenixcontact.com/us/products/0827804>



Alignment tool for cable markers, orange, can be labeled with: BLUEMARK ID COLOR, BLUEMARK ID, BLUEMARK CLED, PLOTMARK, CMS-P1-PLOTTER, mounting type: slide-on, cable diameter range: 2.9 ... 3.6 mm

## UC-WMCO 4,9 (12X5) - Conductor marker

0827733

<https://www.phoenixcontact.com/us/products/0827733>



## BLUEMARK CLED - Printer

5147999

<https://www.phoenixcontact.com/us/products/5147999>



Printers with LED-UV technology for printing plastic labels in UniCard format.

---

Phoenix Contact 2024 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)