


**Live Product Chat** US Only
8:30am - 5pm ET, Mon - Fri

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)



 Active

Always EU RoHS/ELV Compliant (Statement of Compliance)

? Female Screwlock Assembly Kit
? Yellow Chromate Body Finish
? Thread Size = 4 -40
? Thread Length = 7.23 mm
? Screw Length = 11.94 mm

[View all Features](#) | [Find Similar Products](#)

Product Drawings:

- ? [FEMALE SCREWLOCK KIT, SHORT HEAD, .090 PANEL, AMPLIMITE](#) (PDF, English)

? None Available

? None Available

? None Available

[Female Screwlock Kits and Male Screw Retainer Kits](#) (PDF, English)

? None Available

List all Documents

? Product Line Information

? Tooling

Product Type Features:

- ? Product Type = Female Screwlock Assembly Kit
- ? Body Finish = Yellow Chromate
- ? Thread Size = 4 -40
- ? Screw Length (mm [in]) = 11.94 [0.470]
- ? Body Material = Steel
- ? Comment = For Front Panel Mount.; Without Flat Washers

? Screw Finish = Yellow Chromate

? Thread Length (mm [in]) = 7.23 [0.285]

? Screwlock Style = Screwlock With Lockwasher and Hex Nut

- ? Government/Industry Qualification = No
- ? RoHS/ELV Compliance = RoHS compliant, ELV compliant
- ? Lead Free Solder Processes = Not relevant for lead free process
- ? RoHS/ELV Compliance History = Always was RoHS compliant

? Packaging Method = Kit

? Brand = AMP