


UNIT:MM



REVISION INFORMATION			
Rev.	Rev. Date	Modified By	Brief Description
A/0	18-10-15	T1015A	NEW DRAWING

PIN ASSIGNMENT:

P1		P2
1	RED	1
2	WHITE	2
3	GREEN	3
4	BLACK	4
SHELL	DRAIN	SHELL


Electrical test:

1. 100% short, open, miswire test
2. Conduct resistance: 2 Ohm(max)
3. Insulation resistance: 20Mohm(min)
4. dielectric test: DC 300V

CABLE BLACK PRINT

E166160 AWM 2725 80°C 30V
28AWGX1P+24AWGX2C USB2.0

PART NO	WIRE LENGTH "L"	BUYER COLOR	VENDOR COLOR	CUT LENGTH
102-1010-BE-00500	5000±50	BEIGE	IV-29#	4980-5000MM



NO.	NAME	QTY	SPECIFICATION
⑨	PE BAG	1/5	CLEAR SIZE:360X380X0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS"
⑧	PE BAG	1	CLEAR SIZE:150X280X0.05mm PRINT BLACK"MADE IN CHINA"
⑦	TIE	1	WHITE L=120mm
⑥	IN JACKET	3g	CLEAR LDPE (MOULD NO:NM-027)
⑤	OUT JACKET	7g	BEIGE (IV-29#) PVC-55P (MOULD NO:WM-83)
④	OUT JACKET	6g	BEIGE (IV-29#) PVC-55P (MOULD NO:2002-527)
③	CABLE	1	BEIGE (IV-29#) USB2.0 UL2725 28#/1P+24#/2C+AEB OD:4.7mm
②	CONN	1	USB2.0 A FEMALE SHELL:NICKEL PIN G/F SHORT TYPE INSULATOR COLOR:WHITE
①	CONN	1set	USB2.0 A MALE SHELL:MICKEL PIN G/F 3PCS-TYPE INSULATOR COLOR:WHITE

CnC Tech, LLC
Industrial Cable and Connector Technology

DRAWN BY:	DATE: 2018/10/15	DESCRIPTION: 4C CABLE USB A/M+A/F
CHECKED BY:	SHEET 1 of 1	ITEM NO. As above
APPROVED BY:	SCALE 1:1	REV. A/0 UNIT: mm